

1

2

3

4


5

CHARACTERISTICS:

MATERIAL:  
COLOR: BLACK  
OPERATING TEMPERATURE: -20°C UP TO 80°C  
COMPLIANCE: LEAD FREE AND ROHS



PACKAGING:  
10PCS/BAG

WIRE DIMENSION:  
AWG: 24



Terminal A	662 001 137 22
Terminal B	Pre-stripped

\* Note: Wire UL 1007

RoHS Compliant				PROJECTION: 	GENERAL TOLERANCE .X = +/- 0.2 .XX = +/- 0.15	
G						
F						
E						
D						
APPROVAL: RJ				UNIT: MM	DESCRIPTION: WR-MPC3 FEMALE PRE-CRIMPED CONTACT	SIZE <b>A4</b>
C				SCALE:		
B				SHEET: 1/2	WERI PART NO: 662 100 124 015	
A	18-OCT-11	PDF	GG	DRAW: QL		
REV	DATE	FILE	BY			

1

2

3

4

5


A



B

C

D

Note:  
 1.Dimension  
 Carton Size:40\*30\*20(CM)  
 2.Quantity: 5000 Pcs/Carton



RoHS Compliant				PROJECTION: 	GENERAL TOLERANCE .X = +/- 0.2 .XX = +/- 0.15	
G						
F						
E						
D				APPROVAL: RJ	UNIT: MM	DESCRIPTION: WR-MPC3 FEMALE PRE-CRIMPED CONTACT WERI PART NO: 662 100 124 015
C					SCALE:	
B					SHEET: 2/2	
A					DRAW: QL	
REV	DATE	FILE	BY			SIZE <b>A4</b>