

2095GRY

## Specification Grade GFCI Receptacle, Gray - 2095GRY

GFCI Receptacle, 10kA SCCR, 20A/125VAC, Gray



### FEATURES

- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- FSUL Listed (Federal Specification WC596).
- Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.

2095GRY

- Tri-drive screws.
- GFCIs with Auto-Ground assure a positive ground to metal box.

## Specifications

### **DIMENSION INFO**

Width U S: 1.72"

Depth U S: 0.98"

Height U S: 4.2"

### **LISTING AGENCY INFO**

cULus

UL 39121614

### **BUY AMERICAN ACT COMPLIANCE**

Country of Origin: CHINA

Buy American Act Status: No