


M18™ Cordless LITHIUM-ION Band Saw Kit 2629-22

5.0 [Read 3 Reviews](#) [Write a Review](#)

At only 10-1/4lbs and 18" in length, the M18™ Cordless LITHIUM-ION Band Saw Kit is the perfect tool for cutting metal in-place, overhead or in tight spaces. With 3-1/4" cut capacity and low vibration, this saw delivers the cleanest cuts on the most common materials includingq strut, 2-1/2" conduit, 3" angle iron, 3"

Includes

- M18™ Cordless LITHIUM-ION Band Saw 2629-22
- (2) M18™ XC High Capacity RED LITHIUM™ Batteries
- 1-Hour Charger
- Blade
- Case



FEATURES

45% Lighter than Deep Cut – 10.25 Lbs compact light weight design for cutting overhead and in tight places.

3-1/4" Cut Capacity – cuts most common materials for Electrician, Plumber and Mechanical cutting applications. Single pass cut on 3" copper, 3" angle iron, 2-1/2" conduit.

Tool-Free Adjustable Material Shoe – quickly adjusts the shoe and allows flush cuts when working with installed materials against walls and ceilings.

LED Work Light – illuminates the cut line in dark areas.

Blade Ejection System-Quickly change the blade by moving the material guide into the up position and depressing the blade ejection button.

Drop Resistant Pulley Guard-Engineered geometries & high impact polymer.

Cast Aluminum Gear Case-Withstands jobsite abuse & maintains gear positioning.

SPECIFICATIONS

Voltage	18V
SFPM	480
No Load Speed	480
Loaded Speed	390
Max Capacity (Rectangular)	3-1/4" x 3-1/4"
Max Capacity (Round)	3-1/4"
Switch Type	On/Off Trigger
Blade Length	35-3/8"
Batteries Included	2
Length	18"
Tool Weight	10.25 lbs
Shipping Weight	20.0

RELATED ARTICLES

Milwaukee® Introduces
New Compact Band Saws