

List Price \$536.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.****Technical Characteristics**

Features	Operating Mechanism located on Right
Fuse Type	Class J
Horsepower Rating	30HP@240VAC - 60HP@480VAC - 75HP@600VAC
Maximum Voltage Rating	600VAC
Number of Poles	3-Pole
Shaft Type	10mm x 10mm
Terminal Type	Lugs (Kit Required)
Type	GS1
Depth	5.63 Inches
Height	7.19 Inches
Ampere Rating	100A
Approvals	UL Listed - CSA Certified - IEC Rated
Width	8.25 Inches

Shipping and Ordering

Category	22640 - Disconnect Switches, IEC, Type GS1 & LK3
Discount Schedule	I11
GTIN	00785901179580
Package Quantity	1
Weight	6.13 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	TN

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.