



Sta-Kon®

Ferrule

T&B Catalog Number:

F4008

UPC Number:

78621072966

Status:

Active

Description:

Insulated Nylon Ferrule for Wire Size 22, Wire Size 0.34 mm², Length 0.413 inches, Purple


WEB_USE

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

Features

Ferrules ensure reliable electrical connections when terminating conductors in screw clamp terminal blocks.



General

Ferrule Type	Insulated
Insulation Type	Insulated Nylon
Material	Copper
Finish	Electro -Tin Plated
Color	Purple
Wire Range	22
Wire Size (mm ²)	.34

Dimension Information

A (mm)	14.5
B (mm)	6.0
Diameter C (inches)	.031
Diameter C (mm)	0.8
Diameter D (inches)	.079
Diameter D (mm)	2.0
E (mm)	.25
A (inches)	.413
B (inches)	.236
E (inches)	.010

Specifications

Temperature Rating	105°C
Voltage Rating	300V
Flammability Rating	UL 94 V-2

Tooling

Application Tools	T3, ERG2
Recommended Tool	T3, ERG4

Packaging

T&B Order Multiple	500
T&B Inner Pack	500
Package in Units	10000
T&B Sold in UOM	Each
T&B Weight Per UOM	0.2 lbs. per 1000