

High Gain UHF Aerial
DMX05WB



A 32 element, high gain, wideband TV aerial suitable for digital TV applications in medium signal strength areas.



- Enhanced for DTT reception
- Narrow acceptance angle for excellent anti-ghosting properties
- Benchmark Standard 2 approved
- 'Oval bow tie' dipole incorporating an easy fit termination with a soldered brass electrical terminal, braid clamp and a PCB balun for improved gain, impedance match, bandwidth and impulsive noise rejection

- Fortified element reflector design for a superior back to front ratio
- Tilt and side clamp to facilitate adjustment in elevation
- Solid rod X element with rotate-&-lock design
- Easy assembly and installation
- DMX05WB DIY aerial kit also available, includes 10m cable and full fixing accessories

Elements	32	Back/Front Ratio	21dB
Group	Wideband (Ch21-68)	Acceptance Angle	19°
Forward Gain	10.5dB	Length	0.8m

447510.275414

Description	Order Code	Price Each
DMX05WB Aerial	127-1319	
DMX05WB DIY Aerial Kit	127-1320	