

**Linemaster Switch Corporation**

29 Plaine Hill Road POB 238

Woodstock, CT 06281-0238 USA

Toll Free: (800) 974-3668 (US Only) Telephone: (860) 974-1000 Fax: (860) 974-0691

E-Mail: service\_266@linemaster.com Web site: www.linemaster.com

---

## Item # GEM-V3, Gem-V Foot Switch

---



### Gem-V Foot Switch

GEM-V foot switch model feature a round black actuating cap in a chrome plated heavy die cast housing with a full nonskid base pad. Moderate pressure from any direction operates the switch. Standard models supplied with cordset are wired normally open and grounded.

---

## SPECIFICATIONS

Description	Momentary
Circuit	SPST Wired N.O.
Form	A
Electrical Rating	1/2 H.P. 125 VAC 10 A 125 VAC
Standard	EN 60529 Degree of Protection IP20
Size	3 13/16 x 1 7/32 Inch
Weight Approx.	1 lbs
Note	Supplied with 6 ft. 18/3 cord and 3 prong series plug. Green lead grounded.

---