



MODEL CATALOG NO.	310 3018	310C 3022	60 3145	630 3030	630-PL 3050	630-NA 3042	666-R 3066
DC VOLTS							
Milli Volt Range	3000	3000	300	300	250	120 to 600	10
Volt Range	1200	600	1000	600	1000	600 to 1200	1000
No. of Ranges	5	5	8	6	6	14	4
Ohms/Volt Sensitivity	20K	20K	20K	20K	20K	20K	1K
% Accuracy	3	3	1.5	1.5	1.5	1.5	3
AC VOLTS							
Volt Ranges	3 to 1200	3 to 600	3 to 1000	3 to 600	3 to 1000	1.5 to 1200	3 to 1000
No. of Ranges	5	5	6	5	5	10	4
Ohms/Volt Sensitivity	5K	15K	5K	5K	5K	10K	1K
% Accuracy	4	4	3	3	3	3	4
DC CURRENT							
Milli Amp Range	6	6	1	.06	.1	.06	10
Amp Range	6	6	1	.12	10	12	1
No. of Ranges	4	4	4	4	5	12	3
% Accuracy	3	3	1.5	1.5	1.5	1.5	3
RESISTANCE							
K ohm Range	20	20	1	1	1	1	3
Megohm Range	20	20	10	100	100	100	3
No. of Ranges	4	4	5	5	4	6	3
% Accuracy	3	3	1.5	1.5	1.5	1.5	3
POLARITY REVERSING SWITCH		Yes	Yes		Yes	Yes	
OVERLOAD PROTECTED	Yes	Yes	Yes	Yes	Yes	Yes	
AC CLAMP-ON (OPTIONAL)	Yes	Yes	Yes	Yes	Yes	Yes	
INDUSTRIAL NET PRICE	\$82.00	\$112.00	\$189.00	\$175.00	\$195.00	\$280.00	\$130.00



Carrying Cases

- 10-1189 Center flaps snap back allowing full view of scales and permitting complete access to instrument without removal from case. Tester stand available at extra cost.
- 10-1258 Trouser belt slips through loop on back of case for out-of-the-way carrying.
- 10-1456 Has pocket for 101 and accommodates 310-10 series in one combination.
- 10-1791 Flaps back to form handy stand. Test leads store in case and remain plugged in.
- 10-1792 Flaps open to permit use of tester in case. Accessory compartment, built-in stand on back.
- 10-1793 Flaps open to permit use of tester in case. Accessory compartment, built-in stand on back
- 10-2739 Flaps open to permit use of tester in case. Accessory compartment.
- 10-2959 Padded black vinyl pouch case

CARRYING CASE NO.	INDUSTRIAL NET PRICE	FOR USE WITH SERIES	TEST LEAD PART NO.	INDUSTRIAL NET PRICE	FOR USE WITH MODEL NUMBER
10 - 1189	\$42.00	630	79 - 127	\$ 7.00	666-R, 630 & 630A Type 1.
10 - 1258	\$11.50	310			2 & 3, 630PL & 630NA
10 - 1456	\$24.00	310	79 - 153	\$ 8.40	310 SERIES
10 - 1791	\$22.50	666R	79 - 374	\$ 8.90	60 SERIES & 630 Type 4 & Later
10 - 1792	\$25.00	630			
10 - 1793	\$39.00	60 and 630			
10 - 2739	\$39.00	310			
10 - 2959	\$10.50				

