
LTE Blade Antenna

- LTE Blade Antenna
- Multi Frequency Band
- High Gain
- Low V.S.W.R
- Wide temperature range
- High Quality

ADA-0040 Blade Antenna truly challenges antenna design. This antenna covers all the 4G frequency bands together with the 3G and 2G frequencies in one antenna, MAGIC.



RoHS

Specification

Category	Overall performance
Frequency	704MHz ~2620MHz
Bandwith	704 ~ 960MHz // 1710 ~ 2620MHz
Gain	Up to 5.0 dBi
Output Impedance	50 Ω
	Environmental Conditions
Operating Temperature	-40 ~ +80°C
Storage Temperature	-40~+85°C
	Mechanical Data
Connector	SMA Swivel Connector Plug
Dimensions	182 x 30 x 16,3 mm

Ordering codes

TYPE	Description	Comment
ADA-0040	LTE Blade Antenna	4G

For the latest updates, visit our Web site: www.adactus.se

Disclaimer

Information furnished is believed to be accurate and reliable. However, Adactus assumes no responsibility for the consequences of use of such information nor for any infringement of patents or other rights of third parties which may result from its use. Adactus reserves the right to make changes without further notice to any product herein to improve reliability, function or design. Adactus does not assume any liability arising out of the application or use of any product described herein.

This publication supersedes and replaces all information previously supplied. Adactus products are not authorised as critical components in life support devices or systems.