



Tenma 72-9480

Safety Rating

CAT II 600V

CAT III 300V

Certifications

CE

EN:61010-1

EN:61326-1

EN:61010-2-032

Specifications		
Basic Functions	Range	Basic Accuracy
DC Current (A)	40A/600A	$\pm(2.5\%+5)$
AC Voltage (V)	4V/40V/400V/600V	$\pm(1\%+5)$
DC Voltage (V)	400mV/4V/40V/400V/600V	$\pm(0.8\%+1)$
Resistance (Ω)	400 Ω /4K Ω /40K Ω /400K Ω /4M Ω /40M Ω	$\pm(1\%+2)$
Capacitance (F)	4nF/40nF/400nF/4 μ F/40 μ F/100 μ F	$\pm(4\%+3)$
Frequency (Hz)	10Hz ~ 10MHz 10MHz	$\pm(0.5\%+3)$ Reference only
Temperature ($^{\circ}$ C)	-40 $^{\circ}$ C ~ 1000 $^{\circ}$ C	$\pm(2.5\%+3)$
Features		
Display Count		3999
Auto Range		✓
Jaw Capacity		28mm
Diode		✓
Auto Power Off		✓
Continuity Buzzer		✓
Low Battery Indication		✓
Data Hold		✓
MAX Mode		✓
Setup		✓
Input Impedance for DCV	Around 10M Ω	✓

General Characteristic	
Power	9V Battery (6F22)
LCD Size	35.6X 18mm
Product Color	Orange and Grey
Product Net Weight	260g
Product Size	208mm X 76mm X30 mm
Standard Accessories	Battery, Test Lead, Carrying Bag, Point Contact Temperature Probe
Standard Individual Packing	Gift Box, English Manual
Standard Carton Measurement	540mm X 495mm X 335mm (0.09 CBM Per Standard Carton)
Standard Carton Gross Weight	25Kg