

790904-000 Product Details



790904-000

TE Internal Number: 790904-000



SolderShield Cable Splices

 [Always ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Splice
- Splice Type = SolderShield
- Cable Type = Multi-conductor
- Number of Conductors = Single-conductor cable
- Wire Range = 0.50-1.40² [20-16] mm [AWG]

[View all Features](#)

Documentation & Additional Information

Product Drawings:

- [1 to 1 Splices-Crimp SolderShield Splice Kit, Shield...](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

[List all Documents](#)

Additional Product Images:

- [Product View](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Splice
- Splice Type = SolderShield
- [Cable Type](#) = Multi-conductor
- Number of Conductors = Single-conductor cable
- Connection Type = Solder, Crimp

Body Related Features:

- Wire Range (mm [AWG]) = 0.50-1.40² [20-16]
- Conductor Plating = Tin/Silver
- Jacket Outer Diameter (mm [in]) = 4.00 [0.157]

Industry Standards:

- [RoHS/ELV Compliance](#) = ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was ELV compliant

Conditions for Usage:

- Operating Temperature (Max.) (°C) = 150

Operation/Application:

- Application Type = Cable to cable splicing

Other:

- Brand = Raychem