

# Amphenol® LTW®

Amphenol® LTW®



Head Office (Taiwan):  
**Amphenol LTW Technology Co., Ltd.**  
9F, No.657-12, Jungjeng Road, Shinjuang City,  
Taipei County 242, Taiwan  
Tel : +886-2-2908-5626  
Fax: +886-2-2902-9787-88  
e-mail: sales@ltw-tech.com

Branch Office (China):  
**Amphenol Zhengri Electronic (Kunshan) Co., Ltd.**  
No. 62 Da Tung Road, Peng Lang Street, Kunshan City,  
Jiangsu Province 215333, China  
Tel : +86-512-5761-0501-2  
Fax: +86-512-5761-0515  
Sales Contact: (East China) +86-512-5761-0512  
(South China) +86-755-2823-2407  
137-1383-4316

Distributed by :

Amphenol® LTW®

Waterproof Connector Solutions

# Amphenol® LTW® Innovation in Waterproof Solution





## Complete Range of Waterproof Connectors & Cable Assembly

[www.amphenolltw.com](http://www.amphenolltw.com)

Amphenol LTW reserves the right to improve, enhance and modify the design specifications and construction of Amphenol LTW products without prior notification. For additional product and technical information, please contact us.



Copyright by Amphenol LTW in Taiwan 05/2010












SPECIFICATIONS

No.	Specifications	Standard Value
01. Identifications		USB A Type USB B Type
02. Description		Panel Mount, Molded with Cable and Field Installable
03. Current Rating		USB: 1.5A Mini USB: 1A
04. Speed		480Mbps
05. Material		Contacts: Copper Alloy, Gold Plated Connector Body: PBT UL94V-0
06. Temperature Range		-20°C to +80°C
07. Waterproof Rating		IP67, IP68
08. Contact Resistance		≤30mΩ Max
09. Insulation Resistance		≥1000mΩ Min
10. Breakdown Voltage		≥AC 500V / 1 Minute
11. Standard Cable Length (for Molded Cable)		1-5M (Standard Cable: USB2.0)

Male Connector		Mating Parts		Accessories
CONNECTOR	P/N	CONNECTOR	P/N	
 <p><b>1</b></p> <p><b>LTWUA-20PMFP-LC7</b>△</p> <p><b>FEATURES:</b></p> <ul style="list-style-type: none"> <li>• USB A Type</li> <li>• Male Connector</li> <li>• PCB 180°</li> <li>• With or without Flying Lead</li> <li>• IP 67</li> <li>• △ Means Different Versions</li> </ul> <p><b>PANEL CUT-OUT</b></p> 		 <p><b>LTWUA-20AFMM-L</b>△7AXX</p> <p><b>FEATURES:</b></p> <ul style="list-style-type: none"> <li>• USB A Type</li> <li>• Female Connector</li> <li>• Cable Length 1 to 5 Meters</li> <li>• IP 67</li> <li>• △ 180° or 90° In-line Molded Type</li> <li>• With SR</li> </ul>		 <p>Waterproof Cover with Chain</p>
 <p><b>2</b></p> <p><b>LTWUB-20PMFP-LC7</b>△</p> <p><b>FEATURES:</b></p> <ul style="list-style-type: none"> <li>• USB B Type</li> <li>• Male Connector</li> <li>• PCB 180°</li> <li>• With or without Flying Lead</li> <li>• IP 67</li> <li>• △ Means Different Versions</li> </ul> <p><b>PANEL CUT-OUT</b></p> 		 <p><b>LTWUB-20AFMM-L</b>△7AXX</p> <p><b>FEATURES:</b></p> <ul style="list-style-type: none"> <li>• USB B Type</li> <li>• Female Connector</li> <li>• Cable Length 1 to 5 Meters</li> <li>• IP 67</li> <li>• △ 180° or 90° In-line Molded Type</li> <li>• With SR</li> </ul>		 <p>Waterproof Cover with Rubber Lead</p>

Male Connector		Mating Parts 1~3		Accessories
CONNECTOR	P/N	CONNECTOR	P/N	
 <p><b>1</b></p> <p><b>LTWUA-20PMFP-SC8△XX</b></p> <p><b>FEATURES:</b></p> <ul style="list-style-type: none"> <li>• USB A Type</li> <li>• Male Connector</li> <li>• PCB 180°</li> <li>• IP 68</li> <li>• △ With or without Flying Lead</li> </ul> <p><b>PANEL CUT-OUT</b></p> 				 <p>Waterproof Cover with Chain</p>
 <p><b>2</b></p> <p><b>LTWUA-20AMFM-SL7AXX</b></p> <p><b>FEATURES:</b></p> <ul style="list-style-type: none"> <li>• USB A Type</li> <li>• Male Connector</li> <li>• In-line Molded Type</li> <li>• With SR</li> <li>• Cable Length 1 to 5 Meters</li> <li>• IP 67</li> </ul> <p><b>PANEL CUT-OUT</b></p> 		 <p><b>LTWUA-20BFMM-SL7AXX</b></p> <p><b>FEATURES:</b></p> <ul style="list-style-type: none"> <li>• USB A Type</li> <li>• Female Connector</li> <li>• In-line Molded Type</li> <li>• Without SR</li> <li>• Cable Length 1 to 5 Meters</li> <li>• IP 67</li> </ul>		 <p>Waterproof Cover with Rubber Lead</p>
 <p><b>3</b></p> <p><b>LTWUA-20BMFA-SL8001</b></p> <p><b>FEATURES:</b></p> <ul style="list-style-type: none"> <li>• USB A Type</li> <li>• Male Connector</li> <li>• Field Installable</li> <li>• Without Cable</li> <li>• IP 68</li> </ul> <p><b>PANEL CUT-OUT</b></p> 				 <p>Waterproof Cover with Fish Line</p>
				 <p>Waterproof Box</p>

Male Connector		Mating Parts 4~6		Accessories
CONNECTOR	P/N	CONNECTOR	P/N	
 <p><b>4</b></p> <p><b>LTWUB-20PMFP-SC8△XX</b></p> <p><b>FEATURES:</b></p> <ul style="list-style-type: none"> <li>• USB B Type</li> <li>• Male Connector</li> <li>• PCB 180°</li> <li>• IP 68</li> <li>• △ With or without Flying Lead</li> </ul> <p><b>PANEL CUT-OUT</b></p> 				 <p>Waterproof Cover with Chain</p>
 <p><b>5</b></p> <p><b>LTWUB-20AMFM-SL7AXX</b></p> <p><b>FEATURES:</b></p> <ul style="list-style-type: none"> <li>• USB B Type</li> <li>• Male Connector</li> <li>• In-line Molded Type</li> <li>• With SR</li> <li>• Cable Length 1 to 5 Meters</li> <li>• IP 67</li> </ul> <p><b>PANEL CUT-OUT</b></p> 		 <p><b>LTWUB-20BFMM-SL7AXX</b></p> <p><b>FEATURES:</b></p> <ul style="list-style-type: none"> <li>• USB B Type</li> <li>• Female Connector</li> <li>• In-line Molded Type</li> <li>• Without SR</li> <li>• Cable Length 1 to 5 Meters</li> <li>• IP 67</li> </ul>		 <p>Waterproof Cover with Rubber Lead</p>
 <p><b>6</b></p> <p><b>LTWUB-20BMFA-SL8001</b></p> <p><b>FEATURES:</b></p> <ul style="list-style-type: none"> <li>• USB B Type</li> <li>• Male Connector</li> <li>• Field Installable</li> <li>• Without Cable</li> <li>• IP 68</li> </ul> <p><b>PANEL CUT-OUT</b></p> 				 <p>Waterproof Cover with Fish Line</p>
				 <p>Waterproof Box</p>

# 145 USB Screw Style: Mini USB

Male Connector		Mating Parts 1 ~ 4		Accessories
CONNECTOR	P/N	CONNECTOR	P/N	
	<b>1</b> <b>LTWNUB-20PMFP-SC7001</b> <b>FEATURES:</b> <ul style="list-style-type: none"> <li>• Male Connector</li> <li>• PCB 180°</li> <li>• IP 67</li> </ul>			 Waterproof Cover with Chain
	<b>2</b> <b>LTWNUB-20PMFR-SC7001</b> <b>FEATURES:</b> <ul style="list-style-type: none"> <li>• Male Connector</li> <li>• PCB 90°</li> <li>• IP 67</li> </ul>		<b>LTWNUB-20AFMM-SL7AXX</b> <b>FEATURES:</b> <ul style="list-style-type: none"> <li>• Female Connector</li> <li>• In-line Molded Type (Cable to Cable) with SR</li> <li>• Cable Length 5 Meters Max</li> <li>• IP 67</li> </ul>	 Waterproof Cover with Rubber Lead
	<b>3</b> <b>TWNUB-20BMFA-SL7001</b> <b>FEATURES:</b> <ul style="list-style-type: none"> <li>• Male Connector</li> <li>• Field Installable</li> <li>• Without SR</li> <li>• IP 67</li> </ul>			 Waterproof Cover
	<b>4</b> <b>LTWNUB-20AMFM-SL7AXX</b> <b>FEATURES:</b> <ul style="list-style-type: none"> <li>• Male Connector</li> <li>• In-line Molded Type (Cable to Cable) with SR</li> <li>• Cable Length 5 Meters Max</li> <li>• IP 67</li> </ul>			

## PANEL CUT-OUT

