

Heat Resistant Wire

pro-POWER



Specifications:

Voltage Rating	: 1kV AC
Operating Temperature	: 85°C to 105°C
Reel Length (Imperial)	: 328ft
Reel Length (Metric)	: 100m
No. of Strands × Strand Size	: 7 × 0.2mm
Approval Bodies	: BS6360 and BS6746
Conductor Material	: Tinned Copper

Part Number Table

Description	Primary Insulation Colour	Primary Insulation Material	Primary Insulation Thickness	Current Rating (A)	Conductor Area CSA (mm ²)	External Diameter	Conductor Make-up	Part Number
Wire, Heat Resist	Black	PVC	0.45	1.5	0.22	1.5	7/0.2	152433 BLACK 100M
	Red							152435 RED 100M

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell plc 2012.

www.element14.com
www.farnell.com
www.newark.com
www.cpc.co.uk

pro-POWER