







- SPECIFICATIONS:
- Material:
 - Body: PA66
 - Terminal: Brass
 - Threaded Insert: Brass
 - Wire range: N/A
 - Electrical rating: 300V, 8A.
 - Max Torque: N/A.
 - Wire strip length: N/A.
 - Operating temperature: -40C to +105C.
 - $A = (N \times P) + 10.3MM$
 - $B = (N - 1) \times P$
 - $C = (B + 8.6MM)$
 - $P (PITCH) = 3.5MM (.138")$.
 - $N = \text{Number of positions available 2 through 20.}$

RELEASED EC NO: NEO2006-0310 DRWN: LROTHAUS CHKD: CYORK APPR: JPAWLICK A	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ◇=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM/IN		SCALE 4:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION
				mm	INCH	DRAWN BY LROTHAUS	DATE 12/06/05	3.5MM, EURO HEADER VERTICAL, MOUNTING ENDS		
			4 PLACES	± ---	±.0015	CHECKED BY	DATE			
			3 PLACES	±0.038	±.005	C. YORK	01/06/06			
			2 PLACES	±0.13	±.01	APPROVED BY	DATE			
			1 PLACE	±0.3	±---	MOLEX INCORPORATED				
			ANGULAR ± 2 °			MATERIAL NO. SEE CHART		DOCUMENT NO. SD-39505-001		SHEET NO. 1 OF 1
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE B	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

	10	9	8	7	6	5	4	3	2	1																																																																																																																																																																																																																																																																																																																																																																																																																																																																															
F											F																																																																																																																																																																																																																																																																																																																																																																																																																																																																														
E											E																																																																																																																																																																																																																																																																																																																																																																																																																																																																														
D											D																																																																																																																																																																																																																																																																																																																																																																																																																																																																														
C											C																																																																																																																																																																																																																																																																																																																																																																																																																																																																														
B											B																																																																																																																																																																																																																																																																																																																																																																																																																																																																														
A											A																																																																																																																																																																																																																																																																																																																																																																																																																																																																														
<table><tr><th rowspan="4">Description</th><th rowspan="4">Circuit Size</th><th colspan="12">Material Numbers</th><th colspan="6" rowspan="3">Dimensional Information</th></tr><tr><th colspan="6">Black</th><th colspan="6">Green</th></tr><tr><th colspan="3">100% Tin</th><th colspan="3">30 u" Gold</th><th colspan="3">100% Tin</th><th colspan="3">30 u" Gold</th></tr><tr><th colspan="3">Printing Options</th><th colspan="3">Printing Options</th><th colspan="3">Printing Options</th><th colspan="3">Printing Options</th><th colspan="2">Dim. A</th><th colspan="2">Dim B</th><th colspan="2">Dim. C</th></tr><tr><th></th><th></th><th>None</th><th>10AV</th><th>11AV</th><th>None</th><th>10AV</th><th>11AV</th><th>None</th><th>10AV</th><th>11AV</th><th>None</th><th>10AV</th><th>11AV</th><th>mm</th><th>inch</th><th>mm</th><th>inch</th><th>mm</th><th>inch</th></tr><tr><td>3.5mm, Euro Header, Vertical, Mounting ends</td><td>2</td><td>395051002</td><td>395051302</td><td>395051402</td><td>395051502</td><td>395051802</td><td>395051902</td><td>395056002</td><td>395056302</td><td>395056402</td><td>395056502</td><td>395056802</td><td>395056902</td><td>17.30</td><td>0.681</td><td>3.50</td><td>0.138</td><td>12.10</td><td>0.476</td></tr><tr><td>3.5mm, Euro Header, Vertical, Mounting ends</td><td>3</td><td>395051003</td><td>395051303</td><td>395051403</td><td>395051503</td><td>395051803</td><td>395051903</td><td>395056003</td><td>395056303</td><td>395056403</td><td>395056503</td><td>395056803</td><td>395056903</td><td>20.80</td><td>0.819</td><td>7.00</td><td>0.276</td><td>15.60</td><td>0.614</td></tr><tr><td>3.5mm, Euro Header, Vertical, Mounting ends</td><td>4</td><td>395051004</td><td>395051304</td><td>395051404</td><td>395051504</td><td>395051804</td><td>395051904</td><td>395056004</td><td>395056304</td><td>395056404</td><td>395056504</td><td>395056804</td><td>395056904</td><td>24.30</td><td>0.957</td><td>10.50</td><td>0.413</td><td>19.10</td><td>0.752</td></tr><tr><td>3.5mm, Euro Header, Vertical, Mounting ends</td><td>5</td><td>395051005</td><td>395051305</td><td>395051405</td><td>395051505</td><td>395051805</td><td>395051905</td><td>395056005</td><td>395056305</td><td>395056405</td><td>395056505</td><td>395056805</td><td>395056905</td><td>27.80</td><td>1.094</td><td>14.00</td><td>0.551</td><td>22.60</td><td>0.890</td></tr><tr><td>3.5mm, Euro Header, Vertical, Mounting ends</td><td>6</td><td>395051006</td><td>395051306</td><td>395051406</td><td>395051506</td><td>395051806</td><td>395051906</td><td>395056006</td><td>395056306</td><td>395056406</td><td>395056506</td><td>395056806</td><td>395056906</td><td>31.30</td><td>1.232</td><td>17.50</td><td>0.689</td><td>26.10</td><td>1.028</td></tr><tr><td>3.5mm, Euro Header, Vertical, Mounting ends</td><td>7</td><td>395051007</td><td>395051307</td><td>395051407</td><td>395051507</td><td>395051807</td><td>395051907</td><td>395056007</td><td>395056307</td><td>395056407</td><td>395056507</td><td>395056807</td><td>395056907</td><td>34.80</td><td>1.370</td><td>21.00</td><td>0.827</td><td>29.60</td><td>1.165</td></tr><tr><td>3.5mm, Euro Header, Vertical, Mounting ends</td><td>8</td><td>395051008</td><td>395051308</td><td>395051408</td><td>395051508</td><td>395051808</td><td>395051908</td><td>395056008</td><td>395056308</td><td>395056408</td><td>395056508</td><td>395056808</td><td>395056908</td><td>38.30</td><td>1.508</td><td>24.50</td><td>0.965</td><td>33.10</td><td>1.303</td></tr><tr><td>3.5mm, Euro Header, Vertical, Mounting ends</td><td>9</td><td>395051009</td><td>395051309</td><td>395051409</td><td>395051509</td><td>395051809</td><td>395051909</td><td>395056009</td><td>395056309</td><td>395056409</td><td>395056509</td><td>395056809</td><td>395056909</td><td>41.80</td><td>1.646</td><td>28.00</td><td>1.102</td><td>36.60</td><td>1.441</td></tr><tr><td>3.5mm, Euro Header, Vertical, Mounting ends</td><td>10</td><td>395051010</td><td>395051310</td><td>395051410</td><td>395051510</td><td>395051810</td><td>395051910</td><td>395056010</td><td>395056310</td><td>395056410</td><td>395056510</td><td>395056810</td><td>395056910</td><td>45.30</td><td>1.783</td><td>31.50</td><td>1.240</td><td>40.10</td><td>1.579</td></tr><tr><td>3.5mm, Euro Header, Vertical, Mounting ends</td><td>11</td><td>395051011</td><td>395051311</td><td>395051411</td><td>395051511</td><td>395051811</td><td>395051911</td><td>395056011</td><td>395056311</td><td>395056411</td><td>395056511</td><td>395056811</td><td>395056911</td><td>48.80</td><td>1.921</td><td>35.00</td><td>1.378</td><td>43.60</td><td>1.717</td></tr><tr><td>3.5mm, Euro Header, Vertical, Mounting ends</td><td>12</td><td>395051012</td><td>395051312</td><td>395051412</td><td>395051512</td><td>395051812</td><td>395051912</td><td>395056012</td><td>395056312</td><td>395056412</td><td>395056512</td><td>395056812</td><td>395056912</td><td>52.30</td><td>2.059</td><td>38.50</td><td>1.516</td><td>47.10</td><td>1.854</td></tr><tr><td>3.5mm, Euro Header, Vertical, Mounting ends</td><td>13</td><td>395051013</td><td>395051313</td><td>395051413</td><td>395051513</td><td>395051813</td><td>395051913</td><td>395056013</td><td>395056313</td><td>395056413</td><td>395056513</td><td>395056813</td><td>395056913</td><td>55.80</td><td>2.197</td><td>42.00</td><td>1.654</td><td>50.60</td><td>1.992</td></tr><tr><td>3.5mm, Euro Header, Vertical, Mounting ends</td><td>14</td><td>395051014</td><td>395051314</td><td>395051414</td><td>395051514</td><td>395051814</td><td>395051914</td><td>395056014</td><td>395056314</td><td>395056414</td><td>395056514</td><td>395056814</td><td>395056914</td><td>59.30</td><td>2.335</td><td>45.50</td><td>1.791</td><td>54.10</td><td>2.130</td></tr><tr><td>3.5mm, Euro Header, Vertical, Mounting ends</td><td>15</td><td>395051015</td><td>395051315</td><td>395051415</td><td>395051515</td><td>395051815</td><td>395051915</td><td>395056015</td><td>395056315</td><td>395056415</td><td>395056515</td><td>395056815</td><td>395056915</td><td>62.80</td><td>2.472</td><td>49.00</td><td>1.929</td><td>57.60</td><td>2.268</td></tr><tr><td>3.5mm, Euro Header, Vertical, Mounting ends</td><td>16</td><td>395051016</td><td>395051316</td><td>395051416</td><td>395051516</td><td>395051816</td><td>395051916</td><td>395056016</td><td>395056316</td><td>395056416</td><td>395056516</td><td>395056816</td><td>395056916</td><td>66.30</td><td>2.610</td><td>52.50</td><td>2.067</td><td>61.10</td><td>2.406</td></tr><tr><td>3.5mm, Euro Header, Vertical, Mounting ends</td><td>17</td><td>395051017</td><td>395051317</td><td>395051417</td><td>395051517</td><td>395051817</td><td>395051917</td><td>395056017</td><td>395056317</td><td>395056417</td><td>395056517</td><td>395056817</td><td>395056917</td><td>69.80</td><td>2.748</td><td>56.00</td><td>2.205</td><td>64.60</td><td>2.543</td></tr><tr><td>3.5mm, Euro Header, Vertical, Mounting ends</td><td>18</td><td>395051018</td><td>395051318</td><td>395051418</td><td>395051518</td><td>395051818</td><td>395051918</td><td>395056018</td><td>395056318</td><td>395056418</td><td>395056518</td><td>395056818</td><td>395056918</td><td>73.30</td><td>2.886</td><td>59.50</td><td>2.243</td><td>68.10</td><td>2.681</td></tr><tr><td>3.5mm, Euro Header, Vertical, Mounting ends</td><td>19</td><td>395051019</td><td>395051319</td><td>395051419</td><td>395051519</td><td>395051819</td><td>395051919</td><td>395056019</td><td>395056319</td><td>395056419</td><td>395056519</td><td>395056819</td><td>395056919</td><td>76.80</td><td>3.024</td><td>63.00</td><td>2.480</td><td>71.60</td><td>2.819</td></tr><tr><td>3.5mm, Euro Header, Vertical, Mounting ends</td><td>20</td><td>395051020</td><td>395051320</td><td>395051420</td><td>395051520</td><td>395051820</td><td>395051920</td><td>395056020</td><td>395056320</td><td>395056420</td><td>395056520</td><td>395056820</td><td>395056920</td><td>80.30</td><td>3.161</td><td>66.50</td><td>2.618</td><td>75.10</td><td>2.957</td></tr></table>												Description	Circuit Size	Material Numbers												Dimensional Information						Black						Green						100% Tin			30 u" Gold			100% Tin			30 u" Gold			Printing Options			Printing Options			Printing Options			Printing Options			Dim. A		Dim B		Dim. C				None	10AV	11AV	None	10AV	11AV	None	10AV	11AV	None	10AV	11AV	mm	inch	mm	inch	mm	inch	3.5mm, Euro Header, Vertical, Mounting ends	2	395051002	395051302	395051402	395051502	395051802	395051902	395056002	395056302	395056402	395056502	395056802	395056902	17.30	0.681	3.50	0.138	12.10	0.476	3.5mm, Euro Header, Vertical, Mounting ends	3	395051003	395051303	395051403	395051503	395051803	395051903	395056003	395056303	395056403	395056503	395056803	395056903	20.80	0.819	7.00	0.276	15.60	0.614	3.5mm, Euro Header, Vertical, Mounting ends	4	395051004	395051304	395051404	395051504	395051804	395051904	395056004	395056304	395056404	395056504	395056804	395056904	24.30	0.957	10.50	0.413	19.10	0.752	3.5mm, Euro Header, Vertical, Mounting ends	5	395051005	395051305	395051405	395051505	395051805	395051905	395056005	395056305	395056405	395056505	395056805	395056905	27.80	1.094	14.00	0.551	22.60	0.890	3.5mm, Euro Header, Vertical, Mounting ends	6	395051006	395051306	395051406	395051506	395051806	395051906	395056006	395056306	395056406	395056506	395056806	395056906	31.30	1.232	17.50	0.689	26.10	1.028	3.5mm, Euro Header, Vertical, Mounting ends	7	395051007	395051307	395051407	395051507	395051807	395051907	395056007	395056307	395056407	395056507	395056807	395056907	34.80	1.370	21.00	0.827	29.60	1.165	3.5mm, Euro Header, Vertical, Mounting ends	8	395051008	395051308	395051408	395051508	395051808	395051908	395056008	395056308	395056408	395056508	395056808	395056908	38.30	1.508	24.50	0.965	33.10	1.303	3.5mm, Euro Header, Vertical, Mounting ends	9	395051009	395051309	395051409	395051509	395051809	395051909	395056009	395056309	395056409	395056509	395056809	395056909	41.80	1.646	28.00	1.102	36.60	1.441	3.5mm, Euro Header, Vertical, Mounting ends	10	395051010	395051310	395051410	395051510	395051810	395051910	395056010	395056310	395056410	395056510	395056810	395056910	45.30	1.783	31.50	1.240	40.10	1.579	3.5mm, Euro Header, Vertical, Mounting ends	11	395051011	395051311	395051411	395051511	395051811	395051911	395056011	395056311	395056411	395056511	395056811	395056911	48.80	1.921	35.00	1.378	43.60	1.717	3.5mm, Euro Header, Vertical, Mounting ends	12	395051012	395051312	395051412	395051512	395051812	395051912	395056012	395056312	395056412	395056512	395056812	395056912	52.30	2.059	38.50	1.516	47.10	1.854	3.5mm, Euro Header, Vertical, Mounting ends	13	395051013	395051313	395051413	395051513	395051813	395051913	395056013	395056313	395056413	395056513	395056813	395056913	55.80	2.197	42.00	1.654	50.60	1.992	3.5mm, Euro Header, Vertical, Mounting ends	14	395051014	395051314	395051414	395051514	395051814	395051914	395056014	395056314	395056414	395056514	395056814	395056914	59.30	2.335	45.50	1.791	54.10	2.130	3.5mm, Euro Header, Vertical, Mounting ends	15	395051015	395051315	395051415	395051515	395051815	395051915	395056015	395056315	395056415	395056515	395056815	395056915	62.80	2.472	49.00	1.929	57.60	2.268	3.5mm, Euro Header, Vertical, Mounting ends	16	395051016	395051316	395051416	395051516	395051816	395051916	395056016	395056316	395056416	395056516	395056816	395056916	66.30	2.610	52.50	2.067	61.10	2.406	3.5mm, Euro Header, Vertical, Mounting ends	17	395051017	395051317	395051417	395051517	395051817	395051917	395056017	395056317	395056417	395056517	395056817	395056917	69.80	2.748	56.00	2.205	64.60	2.543	3.5mm, Euro Header, Vertical, Mounting ends	18	395051018	395051318	395051418	395051518	395051818	395051918	395056018	395056318	395056418	395056518	395056818	395056918	73.30	2.886	59.50	2.243	68.10	2.681	3.5mm, Euro Header, Vertical, Mounting ends	19	395051019	395051319	395051419	395051519	395051819	395051919	395056019	395056319	395056419	395056519	395056819	395056919	76.80	3.024	63.00	2.480	71.60	2.819	3.5mm, Euro Header, Vertical, Mounting ends	20	395051020	395051320	395051420	395051520	395051820	395051920	395056020	395056320	395056420	395056520	395056820	395056920	80.30	3.161	66.50	2.618	75.10	2.957
Description	Circuit Size	Material Numbers												Dimensional Information																																																																																																																																																																																																																																																																																																																																																																																																																																																																											
		Black						Green																																																																																																																																																																																																																																																																																																																																																																																																																																																																																	
		100% Tin			30 u" Gold			100% Tin			30 u" Gold																																																																																																																																																																																																																																																																																																																																																																																																																																																																														
		Printing Options			Printing Options			Printing Options			Printing Options			Dim. A		Dim B		Dim. C																																																																																																																																																																																																																																																																																																																																																																																																																																																																							
		None	10AV	11AV	None	10AV	11AV	None	10AV	11AV	None	10AV	11AV	mm	inch	mm	inch	mm	inch																																																																																																																																																																																																																																																																																																																																																																																																																																																																						
3.5mm, Euro Header, Vertical, Mounting ends	2	395051002	395051302	395051402	395051502	395051802	395051902	395056002	395056302	395056402	395056502	395056802	395056902	17.30	0.681	3.50	0.138	12.10	0.476																																																																																																																																																																																																																																																																																																																																																																																																																																																																						
3.5mm, Euro Header, Vertical, Mounting ends	3	395051003	395051303	395051403	395051503	395051803	395051903	395056003	395056303	395056403	395056503	395056803	395056903	20.80	0.819	7.00	0.276	15.60	0.614																																																																																																																																																																																																																																																																																																																																																																																																																																																																						
3.5mm, Euro Header, Vertical, Mounting ends	4	395051004	395051304	395051404	395051504	395051804	395051904	395056004	395056304	395056404	395056504	395056804	395056904	24.30	0.957	10.50	0.413	19.10	0.752																																																																																																																																																																																																																																																																																																																																																																																																																																																																						
3.5mm, Euro Header, Vertical, Mounting ends	5	395051005	395051305	395051405	395051505	395051805	395051905	395056005	395056305	395056405	395056505	395056805	395056905	27.80	1.094	14.00	0.551	22.60	0.890																																																																																																																																																																																																																																																																																																																																																																																																																																																																						
3.5mm, Euro Header, Vertical, Mounting ends	6	395051006	395051306	395051406	395051506	395051806	395051906	395056006	395056306	395056406	395056506	395056806	395056906	31.30	1.232	17.50	0.689	26.10	1.028																																																																																																																																																																																																																																																																																																																																																																																																																																																																						
3.5mm, Euro Header, Vertical, Mounting ends	7	395051007	395051307	395051407	395051507	395051807	395051907	395056007	395056307	395056407	395056507	395056807	395056907	34.80	1.370	21.00	0.827	29.60	1.165																																																																																																																																																																																																																																																																																																																																																																																																																																																																						
3.5mm, Euro Header, Vertical, Mounting ends	8	395051008	395051308	395051408	395051508	395051808	395051908	395056008	395056308	395056408	395056508	395056808	395056908	38.30	1.508	24.50	0.965	33.10	1.303																																																																																																																																																																																																																																																																																																																																																																																																																																																																						
3.5mm, Euro Header, Vertical, Mounting ends	9	395051009	395051309	395051409	395051509	395051809	395051909	395056009	395056309	395056409	395056509	395056809	395056909	41.80	1.646	28.00	1.102	36.60	1.441																																																																																																																																																																																																																																																																																																																																																																																																																																																																						
3.5mm, Euro Header, Vertical, Mounting ends	10	395051010	395051310	395051410	395051510	395051810	395051910	395056010	395056310	395056410	395056510	395056810	395056910	45.30	1.783	31.50	1.240	40.10	1.579																																																																																																																																																																																																																																																																																																																																																																																																																																																																						
3.5mm, Euro Header, Vertical, Mounting ends	11	395051011	395051311	395051411	395051511	395051811	395051911	395056011	395056311	395056411	395056511	395056811	395056911	48.80	1.921	35.00	1.378	43.60	1.717																																																																																																																																																																																																																																																																																																																																																																																																																																																																						
3.5mm, Euro Header, Vertical, Mounting ends	12	395051012	395051312	395051412	395051512	395051812	395051912	395056012	395056312	395056412	395056512	395056812	395056912	52.30	2.059	38.50	1.516	47.10	1.854																																																																																																																																																																																																																																																																																																																																																																																																																																																																						
3.5mm, Euro Header, Vertical, Mounting ends	13	395051013	395051313	395051413	395051513	395051813	395051913	395056013	395056313	395056413	395056513	395056813	395056913	55.80	2.197	42.00	1.654	50.60	1.992																																																																																																																																																																																																																																																																																																																																																																																																																																																																						
3.5mm, Euro Header, Vertical, Mounting ends	14	395051014	395051314	395051414	395051514	395051814	395051914	395056014	395056314	395056414	395056514	395056814	395056914	59.30	2.335	45.50	1.791	54.10	2.130																																																																																																																																																																																																																																																																																																																																																																																																																																																																						
3.5mm, Euro Header, Vertical, Mounting ends	15	395051015	395051315	395051415	395051515	395051815	395051915	395056015	395056315	395056415	395056515	395056815	395056915	62.80	2.472	49.00	1.929	57.60	2.268																																																																																																																																																																																																																																																																																																																																																																																																																																																																						
3.5mm, Euro Header, Vertical, Mounting ends	16	395051016	395051316	395051416	395051516	395051816	395051916	395056016	395056316	395056416	395056516	395056816	395056916	66.30	2.610	52.50	2.067	61.10	2.406																																																																																																																																																																																																																																																																																																																																																																																																																																																																						
3.5mm, Euro Header, Vertical, Mounting ends	17	395051017	395051317	395051417	395051517	395051817	395051917	395056017	395056317	395056417	395056517	395056817	395056917	69.80	2.748	56.00	2.205	64.60	2.543																																																																																																																																																																																																																																																																																																																																																																																																																																																																						
3.5mm, Euro Header, Vertical, Mounting ends	18	395051018	395051318	395051418	395051518	395051818	395051918	395056018	395056318	395056418	395056518	395056818	395056918	73.30	2.886	59.50	2.243	68.10	2.681																																																																																																																																																																																																																																																																																																																																																																																																																																																																						
3.5mm, Euro Header, Vertical, Mounting ends	19	395051019	395051319	395051419	395051519	395051819	395051919	395056019	395056319	395056419	395056519	395056819	395056919	76.80	3.024	63.00	2.480	71.60	2.819																																																																																																																																																																																																																																																																																																																																																																																																																																																																						
3.5mm, Euro Header, Vertical, Mounting ends	20	395051020	395051320	395051420	395051520	395051820	395051920	395056020	395056320	395056420	395056520	395056820	395056920	80.30	3.161	66.50	2.618	75.10	2.957																																																																																																																																																																																																																																																																																																																																																																																																																																																																						

SEE SHEET 1 EC NO: NEO2006-0310 DRWN: J.ROTHAUS 2006/01/09 CHKD: C.YORK 2006/01/09 APPR: J.PAWLIK 2006/01/10	QUALITY SYMBOLS ▽=0 ▽=0	REV A	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 4:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		
			4 PLACES ± ---	mm INCH	DRAWN BY LROTHAUS	DATE 12/6/05	TITLE 3.5MM, EURO HEADER VERTICAL, MOUNTING ENDS				
			3 PLACES ± 0.038	±.0015 ±.005	CHECKED BY C. YORK	DATE 01/06/06					
			2 PLACES ± 0.13	±.01	APPROVED BY	DATE					
			1 PLACE ± 0.3		± ---						
			ANGULAR ± 2 °								
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		MATERIAL NO. DOCUMENT NO. SD-39505-001		SHEET NO. 2 OF 2		
					SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				

ib_frame_B_P_ME_T
Rev. D 2004/04/02

| | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | |

SEE SHEET 1
EC NO: NEC02006-0310
DRAWN: LROTHAUS 2006/01/09
CHKD: C.YORK 2006/01/09
APPR: J.PAWLIK 2006/01/10

DESCRIPTION

QUALITY SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± ---	±.0015
3 PLACES	± 0.038	±.005
2 PLACES	± 0.13	±.01
1 PLACE	± 0.3	± ---
ANGULAR ± 2 °		

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM/IN

DRAWN BY
LROTHAUS

DATE
12/6/05

CHECKED BY
C. YORK

DATE
01/06/06

APPROVED BY

DATE

SCALE
4:1

DESIGN UNITS
INCH

THIRD ANGLE
PROJECTION

TITLE
3.5MM, EURO HEADER
VERTICAL, MOUNTING ENDS

MOLEX INCORPORATED

MATERIAL NO.
SEE CHART

DOCUMENT NO.
SD-39505-001

SHEET NO.
2 OF 2

SIZE
B
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION