




**Back**

Selected Cable: 17619				
End View	Plug	Cord	Connector	End View
NONE	NONE	SJT BELDFOIL SHIELDED	2"STRIP	C13

**Cord View**



<b>Part Number</b>	17619
<b>NSN</b>	6150-01-255-3985
<b>Category</b>	3 conductor plastic original equipment cords
<b>Shielding</b>	Beldfoil Shielded
<b>Jacket Color</b>	black
<b>Length Feet</b>	9'10"
<b>Length Meters</b>	3
<b>Temperature Rating</b>	60 C°C
<b>Packaging Units Per Carton</b>	H-100,H-25
<b>Color Coding</b>	International
<b>AWG Stranding</b>	18 (41x34)
<b>Nominal OD Inch</b>	0.34
<b>Nominal OD millimeter</b>	8.63
<b>Rating</b>	1250 Watts 10A-125V (*)
<b>Notes</b>	(*)Dual rated at 10A-250V. See 17621 for 16 gauge version. See 17519 for unshielded version.

**Approvals**



Qty:

Back

Volex Power Cord Products Division, 5350 Lakeview Parkway S. Drive #D Indianapolis, IN 46268  
800-246-CORD. [info@volexpowercords.com](mailto:info@volexpowercords.com)

Proposition 65 warning for California residents: This product contains chemicals, including lead, known to the State of California to cause (cancer, and) birth defects or other reproductive harm. Wash hands after handling.

