

## USB to DVI External Video Card Multi Monitor Adapter – 1920x1200

StarTech ID: *USB2DVIE3*



The USB2DVIE3 USB DVI Video Adapter offers a perfect external multi-monitor solution, enabling you to add a high-resolution (up to 1920x1200) external DVI output to your desktop or laptop computer system using an available USB 2.0 port.

A cost-effective solution for systems that lack the outputs required for a multi-monitor setup, this high-performance USB to DVI adapter can be used to mirror your primary display and show the same image on both screens, or extend your desktop to double your workspace.

This small form factor USB video adapter can be used with up to 4 additional (5 total) USB2DVIE3 USB video adapters, creating multiple DVI connections to add additional displays quickly and easily - all without having to open the computer case to add extra video cards.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Applications

- Add a secondary display adapter and extend your desktop display without taking apart your computer to install a new video card
- Add multiple (up to five) monitors/projectors to your computer setup using one USB2DVI-E3 device for each additional display
- View large or multiple spreadsheets that span multiple displays
- A compact, lightweight solution for traveling business associates using laptop PCs enabling connection to a secondary display
- Connect multiple monitors to a single computer to create engaging multimedia presentations
- Use the adapter to connect your PC to your television for showing family pictures and movies
- Increase productivity by running multiple applications on different screens, check your email on one display and work on a document in the other
- Great for researchers and writers offering the ability to have reference material on one display and a working document copy on the other

## Features

- Supports resolutions up to 1920x1200
- Includes DVI to VGA Adapter and supports the use of DVI to HDMI adapters
- Works with desktop and laptop computers
- No power adapter required, easy installation

Technical Specifications

Warranty	2 Years
Memory	32MB DDR SDRAM
Industry Standards	USB 2.0 Compliant
Chipset ID	MCT T2-285B
Connector A	1 - USB A (4 pin) Male
Connector B	1 - DVH (29 pin) Female
Supported Resolutions	Widescreen(16/32 bit): 1920x1200, 1920x1080, 1680x1050, 1440x900, 1360x768, 1280x800, 1280x768, 1280x720  Standard(16/32 bit): 1600x1200, 1400x1050, 1280x1024, 1280x960, 1152x864, 1024x768, 800x600
Wide Screen Supported	Yes
OS Compatibility	Windows 8 (32/64) Windows 7(32/64) Windows Vista (32/64) Windows XP (32/64) Windows Server 2008 R2 Drivers are WHQL certified
Color	Black
Enclosure Type	Plastic
Cable Length	500 mm [19.7 in]
Product Length	88 mm [3.5 in]
Product Width	52.5 mm [2.1 in]
Product Height	18 mm [0.7 in]
Product Weight	108 g [3.8 oz]
Operating Temperature	-10°C to 55°C (14°F to 131°F)
Storage Temperature	-25°C to 75°C (-14°F to 167°F)
Humidity	<85% RH non condensing
System and Cable Requirements	One available USB 2.0 port
Shipping (Package) Weight	300
Included in Package	1 - USB to DVI Adapter
Included in Package	1 - Driver and Software CD
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

