

Uncontrolled document as of February 20, 2013. Refer to website for up to date specifications.

LIGHTS
2010
SabreLite LED



Submersible 

SabreLite™ 2010 LED Flashlight

The SabreLite 2010 LED is Pelican's flagship LED flashlight. LED technology produces a white collimated beam that's as bright as an incandescent flashlight and provides 10,000 hours of lamp life and extended battery burn time. The rugged, light weight ABS resin body is submersible and a twist on/off lens shroud eliminates accidental discharge. It is powered by 3 C alkaline cells. The SabreLite 2010 Flashlight is the future of LEDs.

Body Material: EXL

Minimum Pack 1 ea.

Package Weight: 7.0 oz.

SabreLite™ 2010 LED Flashlight Specifications

SabreLite™ 2010 LED Flashlight Configurations

Cat. #	Description
2010	SabreLite™ 2010 LED Flashlight (Orange)

2010 SabreLite™ 2010 LED Flashlight (Carded)

2010PL SabreLite™ 2010 LED Flashlight w/ Photoluminescent Shroud






High	
LIGHT SOURCE	LED
BATTERIES	3 C Alkaline (Not included)
CHARGE TIME	N/A
VOLTAGE	4.5
LENGTH	8.11" (20.6 cm)
WEIGHT w/ BATTERIES	13.4 oz. (0.38 kg)
WEIGHT w/o BATTERIES	5.36 oz. (0.15 kg)

NSN List

NSN #	Description
6230-01-530-0810	2010B Black

SabreLite™ 2010 LED Flashlight Accessories

Cat. #	Description
2013PL	Photoluminescent Shroud
8052OR	Traffic Wand (Orange)
8052YW	Traffic Wand (Yellow)

FL1 STANDARD		High	
LIGHT OUTPUT		109 LUMENS	
RUNTIME (hours/min)		32h	
BEAM DISTANCE (meters)		144m	
PEAK BEAM INTENSITY (candela)		5189cd	
WATERPROOF & SUBMERSIBLE		IPX7	IPX7

SabreLite™ 2010 LED Flashlight Approvals

IECEx ITS11.0023 Ex ia IIC T4 Ga (Energizer E93), 145°C (Duracell MN14)



Class I II III Div. 1 Groups ABCDFG Operating Temp. T4 (Energizer E93), 145°C (Duracell MN1400), T3 (Panasonic LR14)

Pelican Products, Inc.

23215 Early Avenue • Torrance, CA 90505 • Phone: (310) 326-4700 • (800) 473-5422 • Fax: (310) 326-3311
e-mail: CSR.Consumer@pelican.com • www.pelican.com