

Uncontrolled document as of February 20, 2013. Refer to website for up to date specifications.



StealthLite™ 2410 LED Flashlight

Same features as the [StealthLite 2400 Flashlight](#) but with the LED module that produces a true, bright collimated LED beam. The 2410 is corrosion proof, resistant to extreme temperatures, and submersible. It is powered by 4 AA alkaline cells (included). For hands-free operation, attach it to your hard hat with our optional helmet light holder.

Body Material: EXL Resin

Minimum Pack 6 ea.

Packaged Weight: 8.4 oz.






StealthLite™ 2410 LED Flashlight Specifications

StealthLite™ 2410 LED Flashlight Configurations

Cat. #	Description
--------	-------------

2410	STEALTHLITE™ 2410 LED FLASHLIGHT (CONT'D)
------	---

High	
LIGHT SOURCE	LED
BATTERIES	4 AA Alkaline (Included)
CHARGE TIME	N/A
VOLTAGE	6
LENGTH	7" (17.8 cm)
WEIGHT w/ BATTERIES	7.3 oz. (0.21 kg)
WEIGHT w/o BATTERIES	3.7 oz. (0.1 kg)

FL1 STANDARD	High	
LIGHT OUTPUT 	126 LUMENS	
RUNTIME (hours:min) 	7h 30m	
BEAM DISTANCE (meters) 	161m	
PEAK BEAM INTENSITY (candela) 	6500cd	
WATERPROOF & SUBMERSIBLE 	IPX7	IPX7

2410 StealthLite™ 2410 LED Flashlight (Carded)

2410PL StealthLite™ 2410 LED Flashlight (35mm) w/ Photoluminescent Shroud

StealthLite™ 2410 LED Flashlight Accessories

Cat. #	Description
700	Helmet Light Holder
710	Helmet Light Holder
711	Helmet Light Holder
712	Helmet Light Holder
750	Helmet Light Holder
760	Helmet Light Holder
770	Universal Helmet Light Holder
2407	Cordura® Holster
2413PL	Photoluminescent Shroud

StealthLite™ 2410 LED Flashlight Approvals

IECEx ITS.09.0017X Ex ia IIC T4 Ga, Ex ia IIIC T135°C Da IP66



Class I II III Div. 1 Grps. ABCDEFG Operating Temp. Class T4

Pelican Products, Inc.

23215 Early Avenue • Torrance, CA 90505 • Phone: (310) 326-4700 • (800) 473-5422 • Fax: (310) 326-3311
e-mail: CSR.Consumer@pelican.com • www.pelican.com