



## RBK HSS JOBBER DRILL 9/64"

**DIN 338/BS 328**

**Flute Geometry** Standard Helix, right hand spiral

**Surface finish** Blue

**Point geometry** Up to 2.9mm - 118° 3.0mm and above - 135° split point

<b>Angle, drill point</b>	118 °
<b>Associated Products</b>	023045
<b>Diameter, drill bit Imperial</b>	9/64 "
<b>Diameter, External</b>	9/64 "
<b>Length, effective</b>	39 mm
<b>Length, overall</b>	70 mm
<b>Material</b>	HSS
<b>RoHS Compliant</b>	NA