



Item no.: 2006-1681/1000-413
 Product description: 2-conductor fuse terminal block for mini-automotive blade-style fuses with test option 24 V with blown fuse indication by LED
 Power consumption LED: 4.8 mA



Produkt kann von Bild abweichen / product may differ

Packing unit 25 pieces

RoHS compliant

Cross section [AWG]	20 - 20 AWG
Cross section to [AWG]	8 AWG
Cross section to [AWG]	8 AWG
Weight	0 g
Width	0.295 in
Cross section [mm ²]	0.5 - 0.5 mm ²
Strip length	0.55 in
Height	1.295 in
Depth	3.791 in
Cross section to [mm ²]	6 mm ²
Width	7.5 mm
Measured shock voltage	8 kV
Cross section to [mm ²]	10 mm ²
Strip length from	13 mm
Strip length to	15 mm
Current intensity EN	25 A
Current intensity EN	30 A
Height	32.9 mm

Depth	96.3 mm
Measured voltage EN	800 V
No. of connection Points	2
No. of potentials	2



Pollution degree	3
Connection method	CAGE CLAMP®S Connection
Wiring method	s + f-st
Connection method	CAGE CLAMP®S Connection
Color	grey
Wiring type	Front-entry
Customs Tariff No.	85369085
Country of Origin	Deutschland
Mounting	TS 35

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected