



Features & Benefits

- Easy to install
- Suitable for Gigabit Ethernet applications
- High Density 24 ports
- Rear cover to protect termination and improve shielding
- Mix and match copper and fibre in one panel
- Manufactured in the UK

Specification

Width	483mm (19")
Depth	98mm
Height	1u (44mm)
Fixing Centre	467mm
Material	Mild steel sheet CR4 to BSEN 10130-1999 DC01
Finish	Matt black polyester paint
Socket Labels	Write-on silk screen on panel front
Cable Management	Improved cabling facility with easy to use cable tie positions for left and right cable entry
IDC Labelling	Colour coded to T568B
IDC Blocks	Industry standard 4 way IDCs
Conforms to	TIA/EIA-568-C.2 Category 6 Specification

Ordering Information

Product Description	Part Number
CCS Cat 6 24 Way 2020 FTP Panel	009-002-002-01

The Connectix Category 6 2020 Series Patch Panel is an alternative to the Standard Category 6 Panel. It offers the same Cat 6 performance as the standard panel but has been designed to present the cable termination IDCs horizontally on a tray at the rear of the panel, making termination and cable management easier.

Category 6 panels provide exceptional performance for high speed LANs including Gigabit Ethernet applications. The boards are designed using the latest noise compensation techniques and the shielding feature minimises the risk of EMI.

All sockets in the panel are commonly linked through the panel and can be grounded to the rack using the earth wire provided. When combined with Connectix Category 6 FTP Modules and Cable the link will perform well in excess of the Category 6 specifications.

LC, SC, ST and FC fibre modules are also available, complete with a Starlight compatible gland hole and integrated management tray. Blank modules can be included for future expansion.

