


Features & Benefits

- ✘ Tamperproof design
- ✘ High Density, Single Gang 4 Port
- ✘ Enhanced Category 5 Performance
- ✘ Designed for direct wall mounting
- ✘ Custom logo service available



Ordering Information

Product Description	Part Number
4030 4 Way Enhanced Cat 5 Tamperproof Wall Outlet	008-001-012-01
4100 Entry Spacer Plate	008-001-013-01

The Connectix 4000 series offers Enhanced Category 5 performance in a high-density package. The position of the sockets allow for a compact installation without protruding leads.


Specification

Width	87mm
Depth	27mm
Height	87mm
Spacer Plate Depth	8mm
Material	ABS thermoplastic resin, with grade UL94 VO at 1.5mm flame retardancy
Finish	High Gloss
IDC Blocks	4 Way Industry Standard IDC blocks
PCB	1.6mm double sided PTH Boards
Conforms to	TIA/EIA-568-B Enhanced Category 5 Specification

The Connectix 4030 outlet restricts the user's access to patch leads, eliminating unauthorised or accidental patch lead disconnection which is one of the most common causes of network problems.

The 4030 is part of the 4000 series product range which are extremely quick and easy to install; just attach the base plate, snap in the PCB, punch down the cables and install the cover. But the 4030 has the added benefit that leads cannot be unplugged without first removing the cover.

Simple Assembly Sequence



The 4000 series outlets have been designed for direct wall mounting with top entry mini trunking, and an optional spacer plate provides side cable entry. In addition, they fit on a standard back box to provide maximum mounting flexibility.