



FIRE & SECURITY



Independently Certified
to EN50131

1 Grade 1

2 Grade 2

3 Grade 3

GRADE 1 CONTACTS


SC517 SC517/WH or BR



- 65 x 13.5 x 13mm
- 5 Terminals
- Operating Gap - 20mm
- EN50131-2-6 Grade 1 Environmental Class II

1

FC509MT2 FC509MT2



- Quick fit metal plated contact
- 25 (dia) x 13 x 57 x 32mm
- 6 Terminal
- Operating Gap - 25mm
- EN50131-2-6 Grade 1 Environmental Class II

1

FC504 FC504/WH or BR



- Quick Fit Flush Contact
- Body 19(dia) x 15 - Face plate 35 x 22mm
- 5 Terminal
- Operating Gap - 18mm
- EN50131-2-6 Grade 1 Environmental Class II

1

FC505 FC505/WH or BR



- Quick Fit Flush Contact
- Body 19(dia) x 15 - Face plate 35 x 22mm
- 5 Terminal
- Operating Gap - 23mm
- EN50131-2-6 Grade 1 Environmental Class II

1

Resistor Table Guide

Type	Resistor Guide	Switch	Tamper
A	Honeywell, Microtech (Galaxy)	1K Ohms	1K Ohms
B	Scantronic, Cooper, Pyronix PCX, Texecom, Castle-Care Tec G3+	4K7 Ohms	2K2 Ohms
C	Guardall (Network 1 configuration) Two wire only	8K2 Ohms	8K2 Ohms
D	DSC	5K6 Ohms	5K6 Ohms
E	Gardtec	6K8 Ohms	4K7 Ohms

Type	Resistor Guide	Switch	Tamper
F	Bosch, DA Abacus	8K2 Ohms	3K9 Ohms
G	Castle Care-Tec	13K Ohms	1K Ohms
H	Europlex, MDT	2K2 Ohms	2K2 Ohms
I	Pyronix Matrix, GE / Aritech, HKC	4K7 Ohms	4K7 Ohms
J	Texecom	22K Ohms	10K Ohms



FireBrand

2Y-LINK



CQR Fire & Security

125 Pasture Road, Moreton, Wirral, CH46 4TH, UK



Sales: 0151 606 1000 Tech: 0151 606 6311 www.cqr.co.uk

info@cqr.co.uk