

CAB CAB ABS 504020 T3B



Sample photo

Order symbol: CAB ABS 504020 T3B
Product nbr: 8183062
Description: Cabinet, ABS
Remarks: Locks on the long side

EAN: 6418074020437
El. number:
 Finland: 3424374
 Denmark: 8212019072
 Italy: 7812060
 Sweden: 2540051
 Norway:

Including: Cabinet base, door with EPDM gasket, 3mm double bit lock(s) with key, screws for mounting plate/DIN-rail and corner plugs.

Dimensions: Length Width Height **Rating:**

mm:	500	400	200
inch:	19.7	15.7	7.9

Ingress Protection (EN 60529): IP 65
 Impact Resistance (EN 62262): IK 08
 Electrical insulation: Totally insulated
 Halogen free (DIN/VDE 0472, Part 815): Yes
 Flammability Rating (UL 746 C 5): UL 94 HB
 Glow Wire Test (IEC 695-2-1) °C: 650
 NEMA Class: NEMA 1, 4, 4X, 12, 13

Materials:

Material:	ABS
Base colour:	RAL 7035
Cover colour:	Smoked grey
Gasket material:	EPDM

Certificates:

Fimko
 Europe EN 62208: 2003
 Gost R

Temperatures:

Short term:	-40 ... 80 °C
Continuous:	-40 ... 60 °C
Short term:	-40 ... 175 °F
Continuous:	-40 ... 140 °F

Accessories:

EKIV 54	Mounting plate
EKIV 37	DIN-35 Mounting rail
DS35370E1	DIN-35 Mounting rail
EKIV 47	DIN-35 Mounting rail
DS35470E1	DIN-35 Mounting rail
FP A 54	Swing-out door/Front plate
MB 12225 AL	Swing door set
FP 54	Front plate
FP 18X2-54	Front plate
DRF 54	DIN rail frame set

