

CARDMASTER PC 25/22-3



Order symbol: PC 25/22-3
Product nbr: 7525134
Description: Enclosure, PC
Remarks: Smoked transparent hinged cover

EAN: 6418074059390
El. number:
 Finland: 3438232
 Sweden: 7525134
 Norway:

Including: Base, terminal compartment cover with EPDM gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Transparent cover with PUR gasket, hinges, locking devices; FC version: Closed PC frame front plate with PUR gasket and cover screws.

Sample photo

Dimensions:		Length	Width	Height	Rating:
mm:		280	219	156	Ingress Protection (EN 60529): IP 65
inch:		11.0	8.6	6.1	Impact Resistance (EN 62262): IK 08/07
Materials:					
Material:		Polycarbonate			
Base colour:		RAL 7035			
Cover colour:		Smoked grey			
Gasket material:		EPDM and Polyurethane			
Temperatures:					
Short term:		-40 ... 120 °C			
Continuous:		-40 ... 80 °C			
Short term:		-40 ... 250 °F			
Continuous:		-40 ... 175 °F			
Certificates:					
Fimko					
Europe EN 62208: 2003					
Gost R					
Accessories:					
MP 25/22		Mounting plate			
FP 25/22		Front plate (aluminium)			
FC PC 25/22		Frame of PC front plate			

