




POLYCARBONATE LANTERNS / PIR LANTERNS



- Requires 1 x suitable ES energy saving lamp (not included)
 - Fittings are rated at 60W max.
 - Polycarbonate construction: corrosion resistant
 - One piece lens: quick & easy assembly
- PIR VERSION**
- 12 metre max detection range
 - Time on 3 minutes +/-20 sec
 - 120° detection zone
 - Factory preset PIR - no override facility



Code	COL	IP	M.O.M	O.P.Q
HL60B Half Lantern	BK	IP44	1	12
HL60WH Half Lantern	WH	IP44	1	12
PIRHL60BK Half Lantern with 120° PIR	BK	IP44	1	12
PIRHL60WH Half Lantern with 120° PIR	WH	IP44	1	12