

BMP™21 Hand-held Label Printer



Why spend time creating labels that are difficult to read and don't stick? With the BMP™21 Hand-held Label Printer, eliminate guesswork and enjoy fast and easy formatting of commonly used label types for marking wire and cable, terminal blocks, patch panels and much more. You can be confident your Brady labels will remain stuck for years. Create clear, legible labels with industrial-strength staying power to withstand even the harshest environments. They won't fall off, smear or fade.

Simple to operate and quick to print, it's a labelling tool specifically designed for industrial environments like voice/datacom, electrical and general industrial. Print one label, knowing it'll adhere and stay legible for the years to come.

The BMP™21 is a labelling solution that lead to increased productivity, supreme accuracy and unrivalled quality for a safer and a more efficient workplace.



Robust Hard wearing Printer

- Hard wearing design for industrial environments
- 203 dpi thermal transfer print
- Large LCD Display (3 lines of text, 1 line of icons)
- Left or right handed cutter activation
- Magnet and pole strap for one-handed operation
- Flashlight accessory for use in confined and low light areas

BMP™21 Label Printer

Article No.	Description
110889	BMP™21 Label Printer
710535	BMP™21 Electrical kit UK
710541	BMP™21 TeleDatacom kit UK
710538	BMP™21 Safety kit UK
710534	BMP™21 Electrical kit EU
710540	BMP™21 TeleDatacom kit EU
710537	BMP™21 Safety kit EU

BMP™21 Accessories

Article No.	Description
110890	BMP™21 Hard Carry Case
110891	BMP™21 Magnet Only Accessory
110892	BMP™21 Multi-functional Accessory
110416	BMP™21 Adaptor EU
110417	BMP™21 Adaptor UK
110937	BMP™21 Adaptor US

Key Features

- Prints on a variety of materials including Continuous Labels and PermaSleeve™ heat shrink sleeves
- Automatic data serialisation and built-in graphics and barcodes
- Access to 80 different symbols, including 48 general identification symbols, 19 electrical symbols including and 13 datacom symbols
- Internal memory for storing, retrieving and deleting label files
- Ergonomic dual cutter buttons that hold the label until you need it
- Six languages (English, Spanish, German, French, Portuguese, Dutch)
- Barcodes (3 of 9 and 128)
- Integrated Smart Cell technology
- Font Autosizing
- Various Accessories (Magnet, Stand, Clip, Strap, Flashlight, Hard Carry Case)



Superior Quality, Long Lasting Labels

- Labels stick and stay to any surface, smooth, curved, textured and highly textured surfaces, even in extreme temperatures.
- Clear accurate labels every time
- Variety of label types to suit any application, wire and cable, terminal blocks, patch panels and much more
- Labels last for up to 5 years in extreme outdoor conditions

Material Selection Guide

BMP™21 Hand-held Label Printer features multiple materials for a variety of applications. Use the chart below to help determine what material works best for your applications.



	Flat, Smooth Surface	Textured, Smooth Surface	Large Curved Surface	Wire & Cable
Self-Laminating Vinyl				
PermaSleeve™				
Nylon Cloth				
Indoor/Outdoor Vinyl				
Polyester				



Self-laminating Vinyl (B-427)

- Self-extinguishing
- Excellent water & oil resistance
- Excellent abrasion resistance

Order Reference	Size (mm, continuous)	Colour
M21-750-427	19.05 x 4.26 m	Black on White
M21-1000-427	25.40 x 4.26 m	Black on White
M21-1250-427	30.48 x 4.26 m	Black on White
M21-1500-427	38.10 x 4.26 m	Black on white



Nylon Cloth (B-499)

IDEAL FOR:

- Wire & Cable
- Terminal blocks
- Patch panels
- Face plates

Order Reference	Size (mm) continuous	Colour
M21-375-499	9.53 x 4.80 m	Black on White
M21-500-499	12.70 x 4.80 m	Black on White
M21-750-499	19.05 x 4.80 m	Black on White



Terminal Block markers (B-499)

Order Reference	Size (mm) continuous	Colour
M21-375-499-TB	9.53 x 4.80 m	Black on White
M21-500-499-TB	12.70 x 4.80 m	Black on White



Polyester (B-423, B-430, B-461 & B-488)

IDEAL FOR:

- Components
- Racks & Bins
- Instruments

Order Reference	Size (mm) continuous	Colour
M21-375-423	9.53 x 6.40 m	Black on White
M21-500-423	12.70 x 6.40 m	Black on White
M21-750-423	19.05 x 6.40 m	Black on White
M21-375-430	9.53 x 6.40 m	Black on Clear
M21-500-430	12.70 x 6.40 m	Black on Clear
M21-750-430	19.05 x 6.40 m	Black on Clear
M21-375-461	9.53 x 6.40 m	Black on White
M21-500-461	12.70 x 6.40 m	Black on White
M21-750-461	19.05 x 6.40 m	Black on White
M21-375-488	9.53 x 6.40 m	Black on White
M21-500-488	12.70 x 6.40 m	Black on White
M21-750-488	19.05 x 6.40 m	Black on White



PermaSleeve™ Wire Marker Sleeves (B-342)

- Heat-shrinkable
- Self-extinguishing
- Meets MIL-M-81531; MIL-STD-202F; method 215 and UL 224

Order Reference	Size (mm) continuous	Colour
M21-125-C-342	5.97 x 2.13 m	Black on White
M21-187-C-342	8.51 x 2.13 m	Black on White
M21-250-C-342	11.15 x 2.13 m	Black on White
M21-375-C-342	16.38 x 2.13 m	Black on white



Indoor/Outdoor Vinyl (B-580)

- Adheres to irregular, curved or rough surfaces
- Stands up to grease, oil and most industrial chemicals
- 5 year average outdoor durability in temperatures from -40°C to 82°C



IDEAL FOR:

- Pipes
- Curved surfaces
- Tools
- Containers
- Bins
- Components
- Instruments
- Panels



Order Reference	Size (mm) continuous	Colour
M21-375-580-WT	9.53 x 6.40 m	Black on White
M21-500-580-WT	12.70 x 6.40 m	Black on White
M21-750-580-WT	19.05 x 6.40 m	Black on White
M21-375-580-YL	9.53 x 6.40 m	Black on Yellow
M21-500-580-YL	12.70 x 6.40 m	Black on Yellow
M21-750-580-YL	19.05 x 6.40 m	Black on Yellow
M21-375-580-BL	9.53 x 6.40 m	White on Blue
M21-500-580-BL	12.70 x 6.40 m	White on Blue
M21-750-580-BL	19.05 x 6.40 m	White on Blue
M21-375-580-GN	9.53 x 6.40 m	White on Green
M21-500-580-GN	12.70 x 6.40 m	White on Green
M21-750-580-GN	19.05 x 6.40 m	White on Green
M21-375-580-OR	9.53 x 6.40 m	Black on Orange
M21-500-580-OR	12.70 x 6.40 m	Black on Orange
M21-750-580-OR	19.05 x 6.40 m	Black on Orange
M21-375-580-RD	9.53 x 6.40 m	White on Red
M21-500-580-RD	12.70 x 6.40 m	White on Red
M21-750-580-RD	19.05 x 6.40 m	White on Red

Brady Europe Locations

Africa	+971 4881 2524	Middle East	+971 4881 2524
Belgium	+32 (0) 52 45 78 11	Norway	+47 70 19 10 30
Denmark	+45 66 14 44 00	Slovakia	+421 2 3300 4800
France	+33 (0) 3 20 76 94 48	Spain	+34 900 902 993
Germany	+49 (0) 6103 7598 660	Sweden	+46 (0) 8 590 057 30
Hungary	+36 23 500 275	Turkey	+90 212 264 02 20
Italy	+39 02 26 00 00 22	UK	+44 (0) 1295 228 288

Your Brady Distributor

