



**RECOMMENDED
PANEL CUT-OUT**

CUSTOMER DRAWING

- NOTES:**
1. INSERTION LOSS: 1.0 dB MAX.
 2. MATERIALS:
HOUSING - DELRIN, BLACK
TOSLINK ADAPTER - ABS
CENTER PIN - BRASS, GOLD PLATED
DUST CAPS - POLYCARBONATE
 3. FOR SCREWS TO BE SHIPPED WITH ASSEMBLY AND INDIVIDUAL PACKAGING, ADD SUFFIX -PKG TO PART NUMBER.
 4. WHEN MOUNTING ASSEMBLY, USE A SCREW TORQUE OF 10 INCH-POUNDS MAXIMUM.
 5. THIS PRODUCT IS RoHS COMPLIANT.

					THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.				
					SIZE	WIDTH	MULT	LBS/M	TEMPER
					FINISH			MATERIAL	
					SPEC No.			SEE NOTES	
					FIRST USED ON		SCALE		
							3:2		
DATE DRAWN		BY	CHKD		APVD				
5/12/08		JGK	RS		TJK				
REV		ECO NUMBER	DATE	BY	APVD	NAME		PART No.	REV
A		26347	2/26/09	RS	TJK	E SERIES		EHTL2	A
REVISIONS					DO NOT SCALE DRAWING				
					TOSLINK ADAPTER, RoHS				

SolidWorks CAD File

