

Telescopic slide rail assembly kit



Product illustrations are exemplary illustrations and can deviate from supplied products.

Part no.: 20860-131

Features:

- Mounting of telescopic slide:
The 19" multipac chassis can be mounted on universal telescopic slides (1 U and 2 U) using the assembly kit
- Assembly kit and adaptor bracket suitable for mounting the multipacPRO chassis in VARISTAR, eurorack and minirack cabinets

Add to basket




Technical Information:

Description

Telescopic slide rail assembly kit

Downloads:

3D PDF with CAD data (STEP) ([Log in](#) required) 

User manual ([Log in](#) required)

To gain access to the additional information you must [log in](#).
If you do not yet have a user name, you may [register here](#).

Delivery comprises:

| Item | Qty | Description |
|------|-----|--|
| 1 | 4 | Mounting bracket, St, zinc-plated; for VARISTAR cabinets |
| 2 | 4 | Mounting bracket, St, zinc-plated; for eurorack cabinets |
| 3 | 4 | Mounting bracket, St, zinc-plated; for minirack cabinets |
| 4 | 1 | Adaptor, St, zinc-plated; for 1 U telescopic slides |
| 5 | 1 | Adaptor, St, zinc-plated; for 2 U telescopic slides |
| 6 | 1 | Assembly kit (cage nuts, nuts, screws, washers) |

Accessories:

| | | |
|--|--|--|
| | | |
|--|--|--|

| Part no. | Description | |
|------------------|--|----------------------|
| 20110-090 | Universal telescopic slide, 1 U Load-carrying capacity P 39 kg, Length L 356 mm, Extension length Y 381 mm, PU 2 piece | Add to basket |
| 20110-091 | Universal telescopic slide, 1 U Load-carrying capacity P 36 kg, Length L 406 mm, Extension length Y 432 mm, PU 2 piece | Add to basket |
| 20110-092 | Universal telescopic slide, 1 U Load-carrying capacity P 34 kg, Length L 457 mm, Extension length Y 483 mm, PU 2 piece | Add to basket |
| 20110-093 | Universal telescopic slide, 1 U Load-carrying capacity P 32 kg, Length L 508 mm, Extension length Y 533 mm, PU 2 piece | Add to basket |
| 20110-094 | Universal telescopic slide, 1 U Load-carrying capacity P 29 kg, Length L 559 mm, Extension length Y 584 mm, PU 2 piece | Add to basket |
| 20110-095 | Universal telescopic slide, 1 U Load-carrying capacity P 27 kg, Length L 610 mm, Extension length Y 635 mm, PU 2 piece | Add to basket |
| 20110-096 | Universal telescopic slide, 1 U Load-carrying capacity P 23 kg, Length L 660 mm, Extension length Y 686 mm, PU 2 piece | Add to basket |
| 20110-097 | Universal telescopic slide, 1 U Load-carrying capacity P 23 kg, Length L 711 mm, Extension length Y 737 mm, PU 2 piece | Add to basket |
| 20110-071 | Slim universal telescopic slide, 2 U Load-carrying capacity P 57 kg, Length L 356 mm, Extension length Y 432 mm, PU 2 piece | Add to basket |
| 20110-072 | Slim universal telescopic slide, 2 U Load-carrying capacity P 55 kg, Length L 406 mm, Extension length Y 483 mm, PU 2 piece | Add to basket |
| 20110-073 | Slim universal telescopic slide, 2 U Load-carrying capacity P 55 kg, Length L 457 mm, Extension length Y 533 mm, PU 2 piece | Add to basket |
| 20110-074 | Slim universal telescopic slide, 2 U Load-carrying capacity P 55 kg, Length L 508 mm, Extension length Y 584 mm, PU 2 piece | Add to basket |
| | | |

| | | |
|------------------|--|----------------------|
| 20110-075 | Slim universal telescopic slide, 2 U Load-carrying capacity P 46 kg, Length L 559 mm, Extension length Y 635 mm, PU 2 piece | Add to basket |
| 20110-076 | Slim universal telescopic slide, 2 U Load-carrying capacity P 46 kg, Length L 584 mm, Extension length Y 660 mm, PU 2 piece | Add to basket |
| 20110-077 | Slim universal telescopic slide, 2 U Load-carrying capacity P 46 kg, Length L 610 mm, Extension length Y 686 mm, PU 2 piece | Add to basket |

Note:

- Please order universal telescopic slides 1 U or universal telescopic slides 2 U, narrow separately