

02 06 200

High Leverage Combination Pliers



- 35 % less effort required than with conventional combination pliers
- easier work due to optimised leverage
- with cutting edges (hardness approx. 63 HRC) for soft and hard wire and piano wire
- long cutting edges for thicker cables
- with gripping zones for flat and round material, suitable for versatile use
- High-grade special tool steel, forged, oil-hardened

Article No.	02 06 200
EAN	4003773010029
Pliers	chrome plated
Handles	insulated with multi-component grips, VDE-tested
Insulation standard	IEC 60900 DIN EN 60900
hard wire Ø mm	2,8
piano wire Ø mm	2,2
Cutting capacity copper cable, multiple-stranded (diameter) Ø mm	13,0
Cutting capacity copper cable, multiple-stranded mm ²	25,0
Length mm	200
Net weight g	343

technical change and errors excepted