

# POTTING BOXES

## 300 Series Multi-Purpose Boxes


An economic range of multi-purpose flame retardant ABS enclosures with deep-profile lid.

- Moulded in UL-94 VO ABS
- Lid mounted by 4x self-tapping screws (smallest & largest sizes snap-fit)
- PCB pillars in base



SPECIFICATION	
Materials	Lid & base ABS, UL-94 VO
Operating temperature	Resistant to temperatures up to 85°C
Standard colours	Light grey similar to RAL 7035 Black similar to RAL 5004
Standard unit includes	Lid & base


BLACK	GREY	LENGTH	WIDTH	HEIGHT	SNAP FIT
BE300-5030B	BE300-5030G	50mm	50mm	30mm	•
BE300-5025B	BE300-5025G	100mm	50mm	25mm	
BE300-5040B	BE300-5040G	100mm	50mm	40mm	
BE300-6540B	BE300-6540G	120mm	65mm	40mm	
BE300-6565B	BE300-6565G	120mm	65mm	66mm	
BE300-1145B	BE300-1145G	185mm	110mm	45mm	•



## 100 Series Open Potting Boxes


Comprehensive range of open top potting boxes. Maximum protection against shock, chemicals, moisture and temperature.

- Encapsulate and protect electronic components
- Moulded in ABS
- Highly resistant to most chemicals
- High rigidity and impact strength
- Compliant with water absorption specifications to DIN53495



SPECIFICATION	
Materials	ABS, UL-94 VO to order
Operating temperature	-20°C to +94°C
Standard colours	Black
Standard unit includes	Box Packs of 10

BLACK	LENGTH	WIDTH	HEIGHT	WALL THICKNESS
RTM101-BLK	25mm	20mm	15mm	1mm
RTM102-BLK	30mm	20mm	15mm	1mm
RTM103-BLK	40mm	35mm	20mm	1mm
RTM104-BLK	50mm	40mm	30mm	1mm
RTM105-BLK	75mm	50mm	35mm	1.4mm
RTM106-BLK	100mm	60mm	25mm	1.5mm
RTM107-BLK	40mm	40mm	20mm	1mm
RTM108-BLK	50mm	50mm	30mm	1mm
RTM109-BLK	11mm	11mm	9mm	0.5mm
RTM110-BLK	22mm	14mm	9mm	0.5mm
RTM111-BLK	30mm	30mm	20mm	1mm
RTM112-BLK	25mm	25mm	25mm	1mm
RTM113-BLK	40mm	40mm	30mm	1mm
RTM114-BLK	75mm	75mm	40mm	1mm
RTM115-BLK	89mm	64mm	33mm	1.5mm
RTM116-BLK	100mm	50mm	25mm	1.3mm



UNIVERSAL ENCLOSURES

HAND HELD CASES

HEAVY DUTY ENCLOSURES

DIN RAIL BOXES

INTERFACE SUPPORTS

CONTROL STATIONS

DIECAST & METAL BOXES

DESKTOP & INSTRUMENT CASES

POTTING BOXES

19" ENCLOSURES

19" SUBRACKS

CUSTOM SIZED ENCLOSURES

CUSTOM SERVICES



+44 (0)1638 716101  
info@camdenboss.com  
www.camdenboss.com

We operate a constant improvement policy, our products are subject to change without notice.

Ver 1.0 Iss 1

**CAMDENBOSS**  
ELECTRONICS & ENCLOSURES