

PRODUCT SPECIFICATION

Brand	C.K
Product Range	HD Classic Screwdrivers

Range Description
A range of professional quality engineers screwdrivers

- Features**
- Cellulose acetate handles – shatterproof and wipe clean
 - Non roll handle design – Specifically designed to stop the screwdrivers rolling off non flat surfaces
 - Toughened high alloy steel blades offering the ultimate in wear resistance and performance
 - Blade torque capacity up to 20% over the International standards requirement
 - Chrome plated shaft with black non peel tip finish for corrosion protection
 - Precision machined tips for the ultimate screw fit and high torque output



Item Number	Item Description
TL14014	HDclassic Screwdriver Slotted Flared Tip 5x75mm
TL14015	HDclassic Screwdriver Slotted Flared Tip 6x100mm
TL14016	HDclassic Screwdriver Slotted Flared Tip 7x125mm
TL14017	HDclassic Screwdriver Slotted Flared Tip 8x150mm

TL14018	HDclassic Screwdriver Slotted Flared Tip 9x200mm
TL14022	HDclassic Screwdriver Slotted Strikethrough 8x150mm
TL14023	HDclassic Screwdriver Slotted Strikethrough 10x200mm
TL14024	HDclassic Screwdriver Slotted Strikethrough 13x250mm
TL14025	HDclassic Screwdriver PH0x65mm
TL14026	HDclassic Screwdriver PH1x80mm
TL14027	HDclassic Screwdriver PH2x100mm
TL14028	HDclassic Screwdriver PH3x150mm
TL14029	HDclassic Screwdriver PH4x200mm
TL14032	HDclassic Screwdriver PZD0x60mm
TL14033	HDclassic Screwdriver PZD1x80mm
TL14034	HDclassic Screwdriver PZD2x100mm
TL14035	HDclassic Screwdriver PZD3x150mm
TL14039	HDclassic Screwdriver Stubby Slotted 6.5x25mm
TL14040	HDclassic Screwdriver Stubby Slotted 8x25mm
TL14042	HDclassic Screwdriver Stubby PH2x25mm
TL14043	HDclassic Screwdriver Stubby PZD1x25mm
TL14044	HDclassic Screwdriver Stubby PZD2x25mm
TL14030	HDclassic Screwdriver Long Reach PH1x250mm
TL14031	HDclassic Screwdriver Long Reach PH2x250mm
TL14037	HDclassic Screwdriver Long Reach PZD1x250mm
TL14038	HDclassic Screwdriver Long Reach PZD2x250mm
TL14045	HDclassic Nut Spinner 4mm
TL14046	HDclassic Nut Spinner 4.5mm
TL14047	HDclassic Nut Spinner 5mm
TL14048	HDclassic Nut Spinner 5.5mm
TL14049	HDclassic Nut Spinner 6mm
TL14050	HDclassic Nut Spinner 7mm
TL14051	HDclassic Nut Spinner 8mm
TL14052	HDclassic Nut Spinner 10mm

Technical product information	<p>Blade/Shaft Made from chrome molybdenum vanadium steel, hardened to 57-59 HRC, Chrome plated with black non peel tip finish. Engineers screwdrivers slotted 5,5; 6,5; 8 and 10mm made from chrome vanadium steel, hardened to 53-55 HRC, black non peel finish.</p> <p>Handle The handle is Cellulose Acetate, injection moulded around the blade. The handles are shatterproof down to -35° C.</p>
-------------------------------	---

Standards compliance	<p>Slotted screwdrivers DIN 5265, DIN 5263, DIN 5264A</p> <p>PZD/SDV Screwdrivers DIN 5262-B-PZ, DIN 5260-PZ, DIN/ISO 8764-1 & 2</p> <p>PH Screwdrivers DIN 5262-B-PH, DIN 5260-PH, DIN/ISO 8764-1 & 2</p>
User health and safety information	Users and bystanders are advised to wear safety goggles
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	<p>HD Comfort Screwdrivers are guaranteed for life against imperfect materials or workmanship</p> <p>Damage caused through inappropriate use is not covered</p>
Country of origin	Germany