

# PRODUCT SPECIFICATION

**Carl  
Kammerling**  
International

<b>Brand</b>	C.K
<b>Product Range</b>	RedLine pliers
<b>Catalogue number</b>	3750, 3751, 3720, 3967, 3803, 3804, 3906, 3907, 3909 & 3754
<b>Date</b>	18/02/2009

**Range Description**  
A range of professional quality pliers and cutters

- Features**
- Hot drop forged from special alloy steel for strength and durability
  - Ergonomically designed sleeves for comfort and effortless use
  - Contoured anti slip shoulders for safety in use
  - Dual compound technology features soft grip non-slip inlays for grip and control
  - Matt chrome finish for corrosion protection
  - Gas/Oil hardened for optimum performance
  - Induction hardened and precision ground cutting edges for precision cutting and long life





Item Number	Item Description
TL12554	C.K RedLine Side cutters 130mm
TL08494	C.K RedLine Side cutters 145mm
TL05885	C.K RedLine Side Cutters 160mm
TL05886	C.K RedLine Side Cutters 180mm
TL12557	C.K RedLine High Leverage Side Cutters 165mm
TL12558	C.K RedLine High Leverage Side Cutters 200mm
TL12555	C.K RedLine Combination Pliers 160mm
TL08495	C.K RedLine Combination Pliers 180mm
TL12559	C.K RedLine Pliers Set Containing 3867 180mm Combination Pliers, 3750 160mm Side cutters &

	3906 200mm Snipe Nose Pliers
T3804	C.K RedLine Pliers Set Containing 3754 160mm Wire Stripping Pliers, 3750 160mm Side cutters & 3906 200mm Snipe Nose Pliers
TL08497	C.K RedLine Snipe Nose Pliers 145mm
TL12556	C.K RedLine Snipe Nose Pliers 200mm
TL08498	C.K Redline Cable Cutters 160mm
CKT3754	C.K Redline Wire Stripping Pliers 160mm

Technical product information	<b>Cutting capacities</b>				
			Cutting Capacity mm diameter wire		
			Hard 2200MPa	Med/Hard 1600MPa	Soft 220MPa
	Item No	Description			
	TL12554	C.K RedLine Side cutters 130mm	1.2	1.6	>4.0
	TL08494	C.K RedLine Side cutters 145mm	1.4	1.9	>4.0
	TL05885	C.K RedLine Side Cutters 160mm	1.6	2.1	>4.0
	TL05886	C.K RedLine Side Cutters 180mm	1.8	2.3	>4.0
	TL12557	C.K RedLine High Leverage Side Cutters 165mm	2.0	2.5	>4.0
	TL12558	C.K RedLine High Leverage Side Cutters 200mm	2.5	3.0	>4.0
	TL12555	C.K RedLine Combination Pliers 160mm	1.6	2.5	>4.0
	TL08495	C.K RedLine Combination Pliers 180mm	1.6	2.5	>4.0
	TL08497	C.K RedLine Snipe Nose Pliers 145mm	1.6	2.0	>4.0
	TL12556	C.K RedLine Snipe Nose Pliers 200mm	1.6	2.0	>4.0
TL08498	C.K Redline Cable Cutter 160mm	-	-	>16.0	
The CKT3754 Wire stripping pliers will strip wires from 0.3 to 5mm diameter					
Standards compliance	Side cutters - DIN ISO 5749 Combination Pliers - DIN ISO 5746 Snipe Nose Pliers - DIN ISO 5745 Wire Stripping Pliers - DIN ISO 5232				
User health and safety information	None applicable				
RoHS/WEEE compliance	These products do not fall within the scope of RoHS or WEEE regulations				
Material safety data	None applicable				
Warranty	C.K tools are guaranteed for life against imperfect materials or workmanship Normal wear and tear or damage caused through inappropriate use is not covered				
Country of origin	Germany				