


## Ink ribbon - THERMOMARK-RIBBON 110 - 5145384

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Ink ribbon, Length: 300000 mm, Width: 110 mm, Color: black

### Key commercial data

|                                      |   |
|--------------------------------------|---|
| Packing unit                         | 1 PCE   |
| GTIN                                 | <br>4 046356 107471 |
| Weight per Piece (excluding packing) | 317.9 GRM   |
| Weight per piece (including packing) | 359.0 GRM   |
| Custom tariff number                 | 96121020  |
| Country of origin                    | China   |
| Sales Key                            | N1 - Tools + Printer  |

### Technical data

#### Dimensions

|            |           |
|------------|-----------|
| Length (b) | 300.00 m  |
| Width (a)  | 110.00 mm |

#### General

|             |          |
|-------------|----------|
| Color       | black    |
| File number | MH 48542 |

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 24190105 |
| eCl@ss 4.1 | 24190105 |
| eCl@ss 5.0 | 19029102 |
| eCl@ss 5.1 | 19029102 |
| eCl@ss 6.0 | 27141137 |
| eCl@ss 7.0 | 27141137 |
| eCl@ss 8.0 | 27141137 |

## Ink ribbon - THERMOMARK-RIBBON 110 - 5145384

### Classifications

#### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC001675 |
| ETIM 5.0 | EC001675 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 43172501 |
| UNSPSC 7.0901 | 43212107 |
| UNSPSC 11     | 43172501 |
| UNSPSC 12.01  | 43212107 |
| UNSPSC 13.2   | 43212107 |