



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: TRAVELER100BT

2 AC outlets, direct plug-in surge suppressor with single line Ethernet or modem/fax surge protection



Highlights

- 2 outlets/Direct plug-in
- 1050 joule rating
- Retractable plug
- Single line Ethernet or modem/fax surge protection
- \$50,000 [Ultimate Lifetime Insurance](#) (USA, Puerto Rico & Canada only)

Description

Tripp Lite's portable TRAVELER100BT surge suppressor offers complete AC and Ethernet or phone line surge suppression for laptops, electronic notepads, personal organizers and other portable electronic devices. Compact portable housing weighing less than 4 ounces neatly fits into laptop travel cases. Retractable plug prevents scratching of expensive portable electronics. Set of RJ45 Ethernet or telephone line suppression jacks protect network lines or dialup and DSL modem lines. TRAVELER100BT offers 2 total outlets in a space saving direct plug-in format and diagnostic LEDs to warn of wiring problems and suppressor damage. \$50,000 [Ultimate Lifetime Insurance](#) (USA & Canada Only).

PLUG/OUTLETS: Input: NEMA5-15P/Output: 2 NEMA5-15R

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA5-15R wall receptacle)

FORMAT: Direct plug-in suppressor hangs off of standard wall socket

SUPPRESSION: AC: 140V RMS Clamping/1050 joules/330V UL1449 Let-through Rating Phone: Single Ethernet or telephone line surge suppression (RJ45 jacks, 2 wire, 1 line)

Applications

- Ideal for use with laptops, electronic notepads, personal organizers and other portable electronic devices.

Package Includes

- TRAVELER100BT Surge Suppressor
- 6-ft. telephone cord
- Instruction manual with warranty information

Features

- 1050 joules AC surge suppression shields equipment from the strongest surges and line noise
- 2 AC outlets with room for 2 transformer plugs without blocking outlets covers computer and one peripheral
- Ethernet or phone line surge suppression protects network lines or dialup and DSL modems, plus fax machines, cordless phones and more (pair of RJ45 jacks, 2 wire, 1 line, includes 6 ft phone cable)
- Exceeds IEEE 587 category A & B surge suppression specifications
- Extra-small portable housing weighing less than 4 ounces neatly fits into laptop travel cases - retractable input plug prevents scratching of

laptops and other devices

- Fail-safe thermal fusing protects against fire and other damage in the event of an extreme, extended overvoltage or surge condition
- Diagnostic LEDs confirm outlet grounding and surge suppression status
- UL1449 Rated (330V all modes), UL1363 (Power Tap), UL497A (Communications), Meets FCC part 68 rules, cUL (Canada)
- \$50,000 [Ultimate Lifetime Insurance](#) (USA and Canada Only)

Specifications

OVERVIEW	
Intended Application	Home/Office, Travel
OUTPUT	
Frequency compatibility	50 / 60 Hz
Output watts	1800
Circuit Breaker (amps)	15
Outlet quantity / type	2 NEMA 5-15R
Transformer accommodation	Supports up to 2 large transformer plug accessories without covering remaining outlets
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input connection type	NEMA 5-15P with retractable input prongs
Input cord length details	Direct plug-in
Voltage compatibility (VAC)	120
Maximum Surge Amps	30000
LEDS ALARMS & SWITCHES	
Diagnostic LEDs	Two built-in LEDs confirm suppressor "protection present" (green) and outlet "grounded" (red) status
SURGE / NOISE SUPPRESSION	
AC suppression joule rating	1050
AC suppression response time	< 1 ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping voltage (RMS)	150
UL1449 let through rating	330V - UL Verified
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	Yes
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	No
Network (Ethernet) Protection	Yes
PHYSICAL	

Shipping Dimensions (HWD/in)	4 x 4 x 1.8
Shipping Dimensions (HWD/cm)	10.2 x 10.2 x 4.6
Shipping weight (lbs)	0.4
Shipping weight (kg)	0.2
Unit Dimensions (HWD/in)	3.5 x 2.5 x 1.75
Unit Dimensions (HWD/cm)	8.9 x 6.4 x 4.4
Unit weight (lbs)	0.3
Unit weight (kg)	0.15
Material of construction	Plastic
Style	Direct Plug-in
Form factors supported	Direct plug-in connection enables mounting to any AC wall receptacle
SPECIAL FEATURES	
Appearance	Ultra-compact, portable suppressor with retractable input plug fits easily in carrying case for laptops and other portable electronics
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449
NOM (Mexico)	NOM
UL1363 (Power Tap)	UL1363
UL497A (Communications)	UL497A
FCC Part 68 (Communications)	FCC Part 68
cUL / CSA (Canada)	cUL
Industry Canada (Communications)	Industry Canada
Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$50,000 Ultimate Lifetime Insurance

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=3055.

Copyright © 2013 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.