



Main

Range of product	C60 IC60 IK60 STI
Product or component type	Comb busbar
Accessory / separate part category	Connection accessory
Poles description	1P
Number of modules	12

Complementary

[In] rated current	Single feed 80 A (40 °C) Double feed 100 A (40 °C)
[Ui] rated insulation voltage	500 V conforming to IEC 664
Mounting mode	Horizontal
9 mm pitches	24

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Compliant - since 0849 - Schneider Electric declaration of conformity
Product environmental profile	Available Download Product Environmental
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Period	18 months
--------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.