


Silver Oxide Battery

SR41



SPECIFICATIONS

| | |
|---------------------------------|-------------------------------|
| Minimum No Load Voltage: | 1.55 V |
| Minimum On Load Voltage: | .49V on 220hms at 1000 |
| Minimum Life | 625 H 23.7k Ohms Hr/Day 1.2 V |
| Rated Capacity | 40 mAh on 23.7kOhms to 1.2V |
| Volume | .18 cm ³ |
| Weight | .65g |

| Physical Size in mm | Max | Min |
|---------------------|-----|------|
| Height/Length | 3.6 | 3.3 |
| Width/Diameter | 7.9 | 7.55 |
| Depth | | |

Typical Discharge Characteristics

