


**PRODUCT
DATA SHEET**

Type	Size	Rating	Description	Part No.
Incandescent	T4.2 x 18	6V 100mA	Wire Terminal, Axial Lamp	3820AL-LF



PHOTOMETRY DATA

PART NO	TEST VOLTS	CURRENT (mA)			LIGHT OUTPUT (Lm)			LIFE (Hours)
		Min.	Nom.	Max.	Min.	Nom.	Max.	
3820AL-LF	6.0	90	100	110	1.426	1.9	2.375	5,000

NOTES:

- 1) C-8 filament shape.
- 2) Leadwire diameter 0.3mm with untinned “cleaned only” finish.
- 3) Lead-free glass

Issue No.	Date	C.N. No.	Drawn	Tech	QA
1	20/06/06	-	BCW	Approved	