



A20 10.1" Horizon Android Tablet PC

Model: NURVODCB



Key Features

Android 4.2 - Jelly Bean
Over 600,000 available apps

**Responsive 10.1" Capacitive
Touch Screen**

Pinch to zoom, twist to rotate
and much more

Powerful Processor

For great gaming

Ultra Thin Form Factor

Fits in a handbag

Product Specification

CPU:	Allwinner Tech A20 Dual- Core, ARM Cortex A7, up to 1.2GHz
Memory:	1GB DDR3 Memory
Storage:	16GB Nand Flash built-in, upgradable to 32GB with TF card slot
Display:	LCD Capacitive Multi-Touch screen, 10.1" High resolution TFT 1024 x 600
Connectivity:	Micro USB, Mini HDMI, Sim, TF card
Audio:	Built-in 1W Speaker, Built-in Mic, 3.5mm Stereo Earphone Jack
Wireless Network:	WiFi IEEE 802.11 b/g/n
Camera:	Front Facing 0.3MP & Rear Facing 2.0MP
Video Supported:	AVI, H.264, DIVX, XVID, rm, rmvb, MKV, WMV, MOV, MP4, MPEG, FLV HD 1080P
Music Supported:	MP3, WMA, MP2, OGG, AAC, M4A, FLAC, 3GP, WAV
Battery:	Up to 6 hrs with Li-ion Battery 5600mAh @ 3.7V
Gyroscope:	Built-in G sensor for gaming and automatic screen rotation
OS:	Google Android 4.2 (Jelly Bean)
Internet Services:	Web browser, JAVA, YouTube, Email, HTML5, Adobe Flash
Utilities:	Calendar, Alarm Clock, Calculator, Recorder, Notepad, Picture Viewer
Dimensions/Weight:	(W) 262mm x (H) 165mm x (D) 12mm / 596g
EAN:	0798295584335