

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [34803-0211](#)
Status: **Active**
Description: CTX64 Female Terminal, D-Wind, Left Payoff, SAE 22

Documents:

Drawing (PDF)	Application Specification AS-560065-001-FR (PDF)
Product Specification PS-502306-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-502306-001 (PDF)	Product Literature (PDF)
Application Specification AS-560065-001 (PDF)	

General

Product Family	Crimp Terminals
Series	34803
Application	Power
Crimp Quality Equipment	Yes
Product Literature Order No	987650-4561
Product Name	CTX64
UPC	884982186613

Physical

Durability (mating cycles max)	10
Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.114/g
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.10 to 1.65mm
Wire Size AWG	22
Wire Size mm ²	0.22-0.35

Electrical

Current - Maximum per Contact	7A
Voltage - Maximum	250V

Material Info

Reference - Drawing Numbers

Application Specification	AS-502306-001, AS-560065-001, AS-560065-001-FR
Product Specification	PS-502306-001
Sales Drawing	SD-31301-053, SD-34803-001



image - Reference only

EU RoHS

**ELV and RoHS
Compliant**
**REACH SVHC
Contains SVHC: No**
**Low-Halogen Status
Low-Halogen**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
 non-product compliance questions.

Search Parts in this Series

[34803Series](#)

Mates With

0.64 by 0.64mm blade

Use With

[34729](#) 2.54mm Pitch Stac64™ Right Angle
 Receptacle

Application Tooling | [FAQ](#)

*Tooling specifications and manuals are
 found by selecting the products below.
 Crimp Height Specifications are then
 contained in the Application Tooling
 Specification document.*

Global

Description	Product #
Hand Crimp Tool for CTX64 Receptacle Terminal, 0.22, 0.30, 0.35mm ² and 22 AWG	0638193700

FineAdjust™ 0639010100
Applicator for
CTX64 Receptacle
Terminals

This document was generated on 10/21/2013

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION