


Model Number

41FY1

Features

- Magnet Actuator
- Compatible with 40FY Series

Dimensions



Technical Data

General specifications

Rated operating distance	s_n	6.4 ... 15.2 mm
Installation		
Output polarity		

Nominal ratings

Indication of the switching state	NO
-----------------------------------	----

Standard conformity

Standards	EN 60947-5-2
-----------	--------------

Ambient conditions

Ambient temperature	-30 ... 70 °C (-22 ... 158 °F)
---------------------	--------------------------------

Mechanical specifications

Housing material	Polycarbonate
Sensing face	Polycarbonate
Protection degree	IP67

Approvals and certificates

UL approval	cULus Listed, General Purpose
CSA approval	cCSAus Listed, General Purpose