

**SOLID PC 1919 13 T**



**Order symbol:** PC 1919 13 T  
**Product nbr:** 5330059  
**Description:** Enclosure, PC  
**Remarks:** Transparent cover

**EAN:** 6418074005397  
**EI. number:**  
 Finland: 3423801  
 Italy: 7402010  
 Sweden: 2539436  
 Norway:

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Sample photo

Dimensions:		Length	Width	Height	Rating:
<b>mm:</b>		188	188	130	Ingress Protection (EN 60529): IP 66/67
<b>inch:</b>		7.4	7.4	5.1	Impact Resistance (EN 62262): IK 08/09
Materials:					
<b>Material:</b>		Polycarbonate			
<b>Base colour:</b>		RAL 7035			
<b>Cover colour:</b>		Clear transparent			
<b>Cover screws material:</b>		Polyamide			
<b>Cover screws colour:</b>		Grey			
<b>Gasket material:</b>		Polyurethane			
Temperatures:					
<b>Short term:</b>		-40 ... 120 °C			
<b>Continuous:</b>		-40 ... 80 °C			
<b>Short term:</b>		-40 ... 250 °F			
<b>Continuous:</b>		-40 ... 175 °F			
Accessories:					
EKHVT		Mounting plate			
EKHXT		Mounting plate Pertinax			
EKV 12		DIN-35 Mounting rail			
					Certificates:
					Underwriters Laboratories
					Fimko
					Europe EN 62208: 2003
					UL Canada
					Gost R
					NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12
					Electrical insulation: Totally insulated
					Halogen free (DIN/VDE 0472, Part 815): Yes
					UV resistance: UL 508
					Flammability Rating (UL 746 C 5): UL 746C 5V
					Glow Wire Test (IEC 695-2-1) °C: 960

