



T&B®

Rigid/IMC Conduit Fittings-Hazardous Location T&B Catalog Number:

UPC Number: EYS1-TB
Status: 78621068629
Description: Active

1/2 in. EYS Sealing Fitting; Body-Ductile Iron; Plug-Gray Iron; Nipple-Steel, Vertical only.

Features

All hubs have a minimum of five full threads, integral bushings to protect conductor insulation from damage, and large access openings for easier packing of sealing material.

Seals are approved to be used with Crouse Hinds® Sealing Compound and Fiber.

Application

EYS sealing fittings can be installed in either vertical or horizontal applications to seal sections of conduit runs from passage of vapors, flame, or gases, to seal off sections of a conduit system during explosion, and limit precompression or pressure piling in conduit system.

General

Material: Ductile Iron
Finish: Zinc Plated

Dimension Information

Hub Size (inches): 1/2
Dimension A (inches): 3.31
Dimension B (inches): 1.25
Dimension C (inches): 1.50
Turning Radius (inches): 1.66

Specifications

3dmodel: Available on Website

Packaging

T&B Inner Pack: 1
Package in Units: 10
T&B Sold in UOM: Each
T&B Weight Per UOM: 116 lbs. per 100

Application Support

T&B Instruction Sheets: ta02366-tb2

Notes

*Note: Class I, Div. 1 & 2, Groups A, B, C, D - Explosion-proof

Certifications

RoHS Compliance: Yes

Certifications



File Nbr:
E 193396

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com