



# T&B<sup>®</sup>

**Rigid/IMC Conduit Fittings**  
**T&B Catalog Number:**

**UPC Number:** H100CAP  
 78621004478  
**Status:** Active  
**Description:**

1 in. Zinc Capoff with thermoplastic insulating throat; sealing ring-Nitrile (BUNA-N). For use with Rigid/IMC Conduit.

**Application**

CSA Certified for hazardous locations Class II  
 Groups E.F.G. Class III.  
 Meets NEMA sealing requirements for NEMA 3R, 4  
 & 13 enclosures.

**General**

Trade Size (inches) 1  
 Material Zinc

**Dimension Information**

Diameter (inches) 2  
 Height (inches) 1 11/16  
 Dimension A (inches) 11/16  
 Dimension B (inches) 1 5/16  
 Dimension C (inches) 1/4

**Specifications**

3dmodel Available on Website

**Packaging**

Package in Units 25  
 T&B Sold in UOM Each  
 T&B Weight Per UOM 29.6 lbs. per 100

**Application Support**

Spacing Chart Available on Website

**Certifications**

RoHS Compliance Yes

**Certifications**



File Nbr:  
 E 23018

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email:techsupport@tnb.com