

Hook Spanner With Hook Nose Fixed



Material

Special steel, hardened, Blackened.
Edgewise ground.

489298

Nut Diameter	Thread Size Of Nut DIN 1804 M	Thread Size Of Nut DIN 981 M	Overall Length(mm)	Thickness (mm)	Order Code	Price Each
30 - 32	14 - 16	20	136	4	137-9052	
34 - 36	18 - 20	-	170	5	137-9051	
40 - 42	22 - 24	-	170	5	137-9049	
45 - 50	26 - 30	30	206	6	137-9046	
58 - 62	38 - 42	40	240	7	137-9043	
68 - 75	45 - 50	55	240	7	137-9040	
80 - 90	52 - 60	60	280	8	137-9038	
95 - 100	62 - 70	-	280	8	137-9035	
110 - 115	72 - 80	85	335	10	137-9032	
120 - 130	85 - 90	90 - 100	335	10	137-9030	