

EcoNetCab

General Telco &
Networking
Enclosures



18U, 22U, 27U, 36U, 42U, & 47U

FREE FITTED ENCLOSURE ACCESSORIES:

- FRONT CABLE MANAGEMENT*
- ROOF-MOUNTED FAN TRAY
- CASTORS & JACKING FEET
- FITTED VENTED SHELF
- SECURING BOLTS



Structured Cabling and Patching



Switch, Routing or PBX



UPS and Broadcast

Redefining quality ergonomics for your telco, networking & PBX needs

Cost-effective and quality enclosures for your structured cabling, networking and broadcast projects.

The LMS Data EcoNetCab is the de-facto standard in offering great choice and quality enclosure solutions, be it structured cabling for your copper or fibre networking, LAN or WAN networking deployment or broadcast A/V for companies of all sizes.

Designed for the installer and IT manager, all enclosure come with useful features to make your installation that much easier, together with bundled free accessories mean you've got everything you need to get your new installation up an running, with minimal fuss or downtime.

enclosures - power distribution - cabling



Copyright 2013 LMS Data

All trademarks acknowledged. E&OE

Specifications subject to change

specifications:

18u CAB-FE-18U-66

600x600x980mm (inc.castors)
ETSI 19" front/rear profiles (adjustable)
Removable side/rear panels, RAL 9005
Front tempered glass door (lockable)

specifications:

22u CAB-FE-22U-66

600x600x1160mm (inc.castors)
ETSI 19" front/rear profiles (adjustable)
Removable side/rear panels, RAL 9005
Front tempered glass door (lockable)

specifications:

27u CAB-FE-22U-66

600x600x1370mm (inc.castors)
ETSI 19" front/rear profiles (adjustable)
Removable side/rear panels, RAL 9005
Front tempered glass door (lockable)

specifications:

36u CAB-FE-36U-66

600x600x1780mm (inc.castors)
ETSI 19" front/rear profiles (adjustable)
Removable side/rear panels, RAL 9005
Front tempered glass door (lockable)

specifications:

42u CAB-FE-42U-66

600x600x2050mm (inc.castors)
ETSI 19" front/rear profiles (adjustable)
Removable side/rear panels, RAL 9005
Front tempered glass door (lockable)

specifications:

18u CAB-FE-18U-68*

600x800x980mm (inc.castors)
ETSI 19" front/rear profiles (adjustable)
Removable side/rear panels, RAL 9005
Front tempered glass door (lockable)

specifications:

22u CAB-FE-22U-68*

600x800x1160mm (inc.castors)
ETSI 19" front/rear profiles (adjustable)
Removable side/rear panels, RAL 9005
Front tempered glass door (lockable)

specifications:

27u CAB-FE-22U-68*

600x800x1370mm (inc.castors)
ETSI 19" front/rear profiles (adjustable)
Removable side/rear panels, RAL 9005
Front tempered glass door (lockable)

specifications:

36u CAB-FE-36U-68*

600x800x1780mm (inc.castors)
ETSI 19" front/rear profiles (adjustable)
Removable side/rear panels, RAL 9005
Front tempered glass door (lockable)

specifications:

42u CAB-FE-42U-68*

600x800x2050mm (inc.castors)
ETSI 19" front/rear profiles (adjustable)
Removable side/rear panels, RAL 9005
Front tempered glass door (lockable)

47u Flat Pack Enclosures also available. Full range specs on request.