

AM 1064
AM 1125

INTEGRATED AMPLIFIERS


| p/n 121.35.081

| p/n 121.35.082



- 60W 3-inputs Mixer-Amplifier (AM 1064)
- 120W 4-inputs Mixer-Amplifier (Am 1125)
- 3 XLR input (AM 1064) 4 XLR input (AM 1125)
- VOX facility and Phantom power supply on input 1
- Audio input 3 also with dual RCA connector
- Aux input on dual RCA connector
- DUCKING Control to adjust the Aux in level
- Audio output (with RCA connector) that sends the same signal routed to the internal amplifier
- Audio input (with RCA connector) to connect an external device directly to the internal power amplifier
- Amplifier output to loudspeakers, available as 100 / 70 V constant voltage line and Low impedance (min. 4 Ω).
- AM 1125 Input for the secondary 24 V dc power supply (batteries)

REAR VIEW



10'000 g
12'000 g
↑ mm

SPECIFICATIONS

	AM 1064 - AM 1125
OUTPUT POWER	60 W (AM 1064) - 120 W (AM 1125)
FREQUENCY RESPONSE	MIC: 60 Hz ÷ 15 kHz - LINE / AUX: 50 ÷ 15 kHz
DISTORTION (THD+N)	< 1.5%
SPEAKER OUTPUTS	100 V, 70 V, 4 Ω
AUXILIARY OUTPUTS	100 V (167 Ω) – 70 V (83 Ω) – 4 Ω
SIGNAL TO NOISE RATIO	> 85 dB
INPUT SENSITIVITY	MIC: 1.5 mV (– 54 dBu) LINE: 200 mV (– 12 dBu)
INPUT IMPEDANCE	600 Ω (balanced)
SUPPLY VOLTAGE	115 V / 230 V ~
POWER CONSUMPTION	170 W
INPUT CONNECTORS	3 x XLR (AM 1064) 4 x XLR (AM 1125), 2 x DOUBLE RCA, 1 x RCA
OUTPUT CONNECTORS	SCREW TERMINALS FOR SPEAKERS, 1 X RCA