

LED Light Kit *FLK LED Series*

Features



- Available in 9",17.5",26",34.5" and 38.5" lengths
- Operating voltage 120V AC 60Hz Operating temperature -20 C to + 50 C
- Long lamp life 60,000 hours in warm white color temperature
- No remote power supplies as unit comes with its own integral LED drivers
- Hard wired via multiple knockouts in light weight extruded Aluminum frame finished white with manual operated switch
- Hinged glass diffuser allows easy access to replaceable LED module

Accessories

Remote Door Switches



| Part Number | Description | Number LED Modules | Energy Use |
|-----------------|---------------------|--------------------|------------|
| FLK5LED | 9" LED Light Kit | 1 | 4.4 w |
| FLK7LED | 17.5" LED Light Kit | 2 | 7.2 w |
| FLK10LED | 26" LED Light Kit | 3 | 9.8 w |
| FLK15LED | 34.5" LED Light Kit | 4 | 15.0 w |
| FLK17LED | 38.5 LED Light Kit | 5 | 17.0 w |

Data subject to change without notice.