



MATERIALS:

Screws: 4 each #4-40 x 6.35 (1/4") Phillips pan head pr MS 35206-213 with blue zinc plating.

Cover: 1.60 (.063) thick aluminum Alloy 1100-H14

Finish: Clear anodized per MIL-A-8625,

Shielded Housing: Die cast aluminum alloy A380 or A384.

Finish: Blue baked enamel per Federal Standard 595 #25109 over primer wash per DOD-P-15328.

RATINGS:

Operating Temperature: +150°C. (+302°F.) Max.

ORDERING INFORMATION: Model 3601

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies.

Made in USA