

## MINIATURE LAMP (44) Details



<b>Part #</b>	<b>44</b>				
<b>Description</b>	<b>T3 1/4 M BAY 6.3V .25A .9CP</b>				
<b>Bulb Shape</b>	T-3 1/4	<b>Filament</b>	C-2R	<b>Base Style</b>	Miniature Bayonet (BA9s)
<b>Glass Diameter (in)</b>	0.39	<b>MOL<sup>†</sup> (in)</b>	1.19	<b>LCL<sup>††</sup> (in)</b>	0.78
<b>Glass Diameter (mm)</b>	10	<b>MOL (mm)</b>	30.20	<b>LCL (mm)</b>	19.80
<b>Volts</b>	6.3	<b>MSCP<sup>‡</sup></b>	0.9	<b>Avg Life Hrs</b>	3000
<b>Watts</b>	1.575	<b>Amps</b>	0.25	<b>RoHS Compliant</b>	

**† MOL (Maximum Overall Length):**

The overall length of a lamp, from the top of the shell to the bottom of the base.

**‡ MSCP (Mean Spherical Candlepower):**

Candlepower produced at design volts. Candlepower is increased rapidly with an increase of applied voltage and conversely is reduced rapidly with a reduction of applied voltage.

**†† LCL (Light Center Length):**

The distance from a reference point, usually the bottom of the lamp base, to the center of the light source.